



FHD-MCL-11-SS

Ruland FHD-MCL-11-SS, 11mm Face Mount Shaft Collar with Drilled Hole,
303 Stainless Steel, One-Piece Clamp Style, 28mm OD, 11mm Width



Description

Ruland FHD-MCL-11-SS is a one-piece shaft collar with a 11mm bore, 28mm OD, and 11mm width. FHD-MCL-11-SS has drilled holes for mounting shaft collars to sprockets, pulleys, metallic plates, or other components. Drilled holes give the user flexibility to choose inch or metric mounting hardware that best suits the application. The clamp style design does not mar the shaft, is easy to remove, and is indefinitely adjustable. Equipment manufacturers benefit from the tightly controlled face to bore perpendicularity (TIR of ? .05mm). Perpendicularity is critical for alignment when the shaft collar is used as a load bearing face, mechanical stop, or for mounting components such as gears or bearings. Proprietary processes have been developed by Ruland to maintain superior fit, finish, and holding power. FHD-MCL-11-SS is stamped with the Ruland name and bore size for ease of identification. Forged screws test beyond DIN 912 12.9 standards to ensure maximum holding power. FHD-MCL-11-SS is machined from solid bar stock to a fine burr free finish and sourced exclusively from North American mills. Ruland uses 303 stainless steel with hardware of like material for consistent corrosion resistance. It is RoHS3 and REACH compliant and manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore (B1)	11 mm	Bore Tolerance	+0.050 mm / +0.012 mm
Outer Diameter (OD)	28 mm	Clearance Diameter (C) MAX	32.0 mm
Width (W)	11 mm	Width Tolerance	+0.076 mm / -0.254 mm
Hole to Center (HC)	9.75 mm	Hole to Hole (HH)	19.50 mm
Hole Diameter (H)	4.31 mm	Recommended Shaft Tolerance	+0.000 mm / -0.013 mm
Forged Clamp Screw	M4 x 12	Screw Material	18-8 300 Series Stainless Steel
Hex Wrench Size	3.0 mm	Screw Finish	Bright
Seating Torque	2.5 Nm	Screw Location (R)	10.01 mm
Number of Screws	1 ea	Torque Wrench	TW:BT-1R-1/4-22.6
Recommended Hex Key	Metric Hex Keys	Material Specification	Type 303 Austenitic, Non-Magnetic Bar
Temperature	-40°F to 350°F (-40°C to 176°C)	Finish Specification	Bright, No Plating
Manufacturer	Ruland Manufacturing	Country of Origin	USA
Weight (lbs)	0.087980	UPC	63452937619
Tariff Code	8483.60.8000	UNSPC	31162811
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	WARNING This product can expose you to the chemical Nickel (metallic), known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov .		