

FEATURES

- **High chemical resistance:** Suitable for use with a wide range of chemicals, enhancing versatility
- **Maximum operating pressure of 3000 kPa:** Ensures reliable sealing in high-pressure applications
- **Maximum operating temperature of 280 °C:** Suitable for high-temperature environments
- **Rotary speed of 18 m/s:** Capable of handling high-speed rotary applications
- **Section size of 10 mm:** Provides a robust and secure seal
- **Length of 8 m:** Offers ample material for various applications

RS PRO 10mm Gland Packing, Polytetrafluoroethylene

RS Stock No: 606-546



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland packing is designed for sealing applications in various industrial environments. Made from high-quality polytetrafluoroethylene, it offers excellent chemical resistance and durability. Ideal for use in high-pressure and high-temperature settings, this gland packing ensures reliable performance and longevity.

General Specifications

Maximum Operating Pressure	3000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	18 m/s
Section	10 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polytetrafluoroethylene

Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, BAM, FDA, RoHS
---------------------	--------------------------------------