



FLAMESTAT HIGH VIS MATERNITY STRETCH TROUSERS CLASS 2 2507 ATHF

ART. NO: 133137

Stretch fabric / Dirt, oil and water repellent / Upper part in heavy rib-knitted 4-way stretch tricot with soft inserted elastic at top / Adjustable waistband with built-in elastic / Waistband with low cut front, belt loops, button but no zipper / 2 front pockets / 2 reinforced back pockets, one with flap and concealed snap fastening / Hammer loop / Reinforced folding rule pocket with pen pocket and button and loop for sheath knife / Leg pocket with flap and concealed snap fastening, mobile phone pocket and loops for ID card holder / Reinforced knee pockets with inside opening / Height adjustment for knee pads in knee pocket / Reinforced leg ends / Metal free / Approved according to EN 61482-1-2 APC 1, EN 61482-1-1 ELIM: 8 cal/cm² (included in electric arc certified garment combinations), EN ISO 11612 A1 B1 C1 F1, EN 1149-5, EN ISO 20471 class 2 and EN 14404 together with kneepads 124292 / Fabric is approved according to EN 13034 / Certified after 50 washes / Laundry-tested according to ISO 15797 / OEKO-TEX® certified.

Material: Stretch 45% modacrylic, 34% cotton, 17% polyamide, 2% elastane, 2% anti-static fibre.

Rib-knit stretch 59% modacrylic, 36% cotton, 3% elastane, 2% anti-static fibre.

Reinforcement 45% modacrylic, 35% cotton, 18% polyamide, 2% anti-static fibre.

Inherent flame protection. In transition to PFAS free.

Weight: Stretch 265 g/m². Rib-knit stretch 440 g/m². Reinforcement 300 g/m².

Color: F171 High vis Yellow/Navy

Size: 34-50



PRO **T3**

EN 11612 EN 1149-5 IEC 61482-2 EN 20471 EN 14404

SIZES MAY VARY BETWEEN COLORS
Print date: 2025-09-04

FRISTADS®