

# R79 Series Single Metallized Polypropylene Film, Radial, 5 mm Lead Spacing, Multipurpose Applications

## Overview


The R79 Series is constructed of metallized polypropylene film with radial leads of tinned wire. The radial leads are electrically welded to the metal layer on the ends of the capacitor winding. The capacitor is encapsulated with a self-extinguishing thermosetting resin in a box material meeting the UL 94V-0 requirements.

## Applications

Typical applications include timing, oscillator circuits, high frequency coupling and decoupling applications. Not suitable for across-the-line application (see Suppressor Capacitors).

## Benefits

- Voltage range: 160 – 630 VDC
- Capacitance range: 0.001 – 0.22  $\mu$ F
- Lead Spacing: 5 mm
- Capacitance tolerance:  $\pm$ 5%,  $\pm$ 10%,  $\pm$ 20%
- Climatic category: 55/105/56 IEC 60068-1
- Operating temperature range of  $-55^{\circ}\text{C}$  to  $+105^{\circ}\text{C}$
- RoHS compliance and lead-free terminations
- Tape and reel packaging in accordance with IEC 60286-2
- Self-healing




## Part Number System

| R79                      | G  | C                 | 2390  | AA                         | 40           | K   |
|--------------------------|--|-------------------|---|----------------------------|--------------|---|
| Series                   | Rated Voltage (VDC)                      | Lead Spacing (mm) | Capacitance Code ( $\mu$ F)   | Packaging                  | Internal Use | Capacitance Tolerance                     |
| Metallized Polypropylene | G = 160<br>I = 250<br>M = 400<br>P = 630 | C = 5             | The last three digits represent significant figures. The first digit specifies the total number of zeros to be added. | See Ordering Options Table | 40<br>45     | H = 2.5%<br>J = $\pm$ 5%<br>K = $\pm$ 10% |

## Ordering Options Table

| Lead Spacing Nominal (mm) | Type of Leads and Packaging                      | Lead Length (mm)   | Lead and Packaging Code |
|---------------------------|--|--------------------|-------------------------|
| 5                         | <b>Standard Lead and Packaging Options</b>       |                    |                         |
|                           | Bulk (Bag)–Short Leads                           | 4 +1.5/-0          | AA                      |
|                           | Ammo Pack  | $H_0=18.5 \pm 0.5$ | DQ                      |
|                           | <b>Other Lead and Packaging Options</b>          |                    |                         |
|                           | Tape & Reel (Standard Reel $\varnothing$ 355 mm) | $H_0=18.5 \pm 0.5$ | CK                      |
|                           | Bulk (Bag)–Short Leads                           | 10 $\pm$ 1         | JC                      |
|                           | Bulk (Bag)–Short Leads                           | 4.0 +0.5/-0        | JE                      |
|                           | Bulk (Bag)–Short Leads                           | 3.2 +0.3/-0.2      | JH                      |
| Bulk (Bag)–Long Leads     | 17 +1/-2   | Z3                 |                         |

## Dimensions – Millimeters




| p       |           | B       |           | H       |           | L       |           | d       |            |
|---------|-----------|---------|-----------|---------|-----------|---------|-----------|---------|------------|
| Nominal | Tolerance | Nominal | Tolerance | Nominal | Tolerance | Nominal | Tolerance | Nominal | Tolerance  |
| 5.0     | $\pm 0.4$ | 3.5     | +0.1      | 7.5     | +0.1      | 7.2     | +0.2      | 0.6     | $\pm 0.05$ |
| 5.0     | $\pm 0.4$ | 4.5     | +0.1      | 9.5     | +0.1      | 7.2     | +0.3      | 0.6     | $\pm 0.05$ |
| 5.0     | $\pm 0.4$ | 5.0     | +0.1      | 10.0    | +0.1      | 7.2     | +0.3      | 0.6     | $\pm 0.05$ |
| 5.0     | $\pm 0.4$ | 6.0     | +0.1      | 11.0    | +0.1      | 7.2     | +0.3      | 0.6     | $\pm 0.05$ |
| 5.0     | $\pm 0.4$ | 7.2     | +0.1      | 13.0    | +0.1      | 7.2     | +0.3      | 0.6     | $\pm 0.05$ |

Note: See Ordering Options Table for lead length (LL/Ho) options.

## Performance Characteristics

|                                     |  |              |                |               |  |
|-------------------------------------|--|--------------|----------------|---------------|--|
| Dielectric                          | Polypropylene film   |              |                |               |  |
| Plates                              | Metal layer deposited by evaporation under vacuum  |              |                |               |  |
| Winding                             | Non-inductive type   |              |                |               |  |
| Leads                               | Tinned wire  |              |                |               |  |
| Protection                          | Plastic case, thermosetting resin filled. Box material is solvent resistant and flame retardant according to UL94. |              |                |               |  |
| Related Documents                   | IEC 60384-16   |              |                |               |  |
| Rated Voltage $V_R$ (VDC)           | 160  | 250          | 400            | 630           |  |
| Rated Voltage $V_R$ (VAC)           | 70   | 160          | 200            | 220           |  |
| Capacitance Range ( $\mu\text{F}$ ) | 0.039 – 0.22   | 0.012 – 0.15 | 0.0039 – 0.047 | 0.001 – 0.018 |  |
| Capacitance Values                  | E12 series (IEC 60063) measured at 1 kHz and +20 $\pm$ 1°C   |              |                |               |  |
| Capacitance Tolerance               | $\pm$ 2.5%, $\pm$ 5%, $\pm$ 10%  |              |                |               |  |
| Operating Temperature Range         | -55°C to +105°C  |              |                |               |  |
| Rated Temperature $T_R$             | +85°C  |              |                |               |  |
| Voltage Derating                    | Above +85°C DC and AC voltage derating is 1.25%/°C   |              |                |               |  |
| Climatic Category                   | 55/105/56 IEC 60068-1  |              |                |               |  |
| Storage Conditions                  | Storage time: $\leq$ 24 months from the date marked on the label package   |              |                |               |  |
|                                     | Average relative humidity per year $\leq$ 70%  |              |                |               |  |
|                                     | RH $\leq$ 85% for 30 days randomly distributed throughout the year   |              |                |               |  |
|                                     | Dew is absent  |              |                |               |  |
|                                     | Temperature: -40 to 80°C (see "Maximum Humidity in Storage Conditions" graph below)                                |              |                |               |  |

### Maximum Humidity in Storage Conditions







## Performance Characteristics cont'd





|                         |   |            |          |
|-------------------------|---|------------|----------|
| Test Voltage            | 1.6 x V <sub>R</sub> VDC for 2 seconds (between terminations) @ +25°C ±5°C  |            |          |
| Capacitance Drift       | Maximum 0.5% after a 2 year storage period at a temperature of +10°C to +40°C and a relative humidity of 40% to 60%   |            |          |
| Maximum Pulse Steepness | dV/dt according to Table 1. For peak to peak voltages lower than rated voltage (V <sub>pp</sub> < V <sub>R</sub> ), the specified dv/dt can be multiplied by the factor V <sub>R</sub> /V <sub>pp</sub> |            |          |
| Temperature Coefficient | -(200 ±100) ppm/°C at 1 kHz   |            |          |
| Self Inductance         | Approximately 6 nH. Maximum 1 nH per 1 mm lead and capacitor length.  |            |          |
| Dissipation Factor tanδ | Maximum Values at 25°C ±5°C   |            |          |
|                         | Frequency   | C ≤ 0.1 μF | C > 1 μF |
|                         | 1 kHz   | 0.06%      | 0.06%    |
|                         | 10 kHz  | 0.10%      | 0.10%    |
|                         | 100 kHz   | 0.30%      | -        |
| Insulation Resistance   | Measured at +25°C ±5°C, 100 VDC 60 seconds  |            |          |
|                         | Minimum Values Between Terminals  |            |          |
|                         | All Capacitance Values  |            |          |
|                         | ≥ 100,000 MΩ<br>(≥ 500,000 MΩ)*   |            |          |

\* Typical value

## Maximum Voltage ( $V_{rms}$ ) vs. Frequency (Sinusoidal Waveform/ $Th \leq 40^\circ C$ )



## Maximum Current ( $I_{rms}$ ) vs. Frequency (Sinusoidal Waveform/ $T_h \leq 40^\circ\text{C}$ )



## Environmental Test Data

| Damp Heat, Steady State Test      | Test Conditions:                 |                            | Performances  |
|-----------------------------------|----------------------------------|----------------------------|---|
|                                   | Temperature:                     | +40°C ± 2°C                | Δ C/C  ≤ 3%,<br>Δ tanδ ≤ 0.001 at 1 kHz<br>IR after test ≥ 50% of initial limit       |
|                                   | Relative humidity (RH):          | 93% ± 2%                   |   |
|                                   | Test duration:                   | 56 days                    |   |
| Endurance Test                    | Test Conditions                  |                            | Performances  |
|                                   | Temperature:                     | +85°C ± 2°C                | Δ C/C  ≤ 3%,<br>Δ tanδ ≤ 0.001 at 10 kHz<br>IR after test ≥ 50% of initial limit      |
|                                   | Voltage applied:                 | 1.25 x V <sub>R</sub> (DC) |   |
|                                   | Test duration:                   | 2,000 hours                |   |
| Resistance to Soldering Heat Test | Test Conditions                  |                            | Performances  |
|                                   | Solder bath temperature:         | 260°C ± 5°C                | Δ C/C  ≤ 2%,<br>Δ tanδ ≤ 0.001 at 10 kHz for C ≤ 1μF<br>IR after test ≥ initial limit |
|                                   | Dipping time (with heat screen): | 10 seconds ± 1 second      |   |

## Environmental Compliance

All KEMET pulse capacitors are RoHS Compliant.

**Table 1 – Ratings & Part Number Reference**

| VDC | VAC | Capacitance Value (µF) | Dimensions in mm |        |        | Lead Spacing (p) | dV/dt (V/µs) | Max K <sub>0</sub> (V <sup>2</sup> /µs) | New KEMET Part Number | Legacy Part Number |
|-----|-----|------------------------|------------------|--------|--------|------------------|--------------|---|-----------------------|--------------------|
|     |     |                        | B                | H      | L      |                  |              |   |                       |                    |
| 160 | 70  | 0.039                  | 3.5              | 7.5    | 7.2    | 5.0              | 100          | 32,000                                  | 79GC2390(1)40(2)      | R79GC2390(1)40(2)  |
| 160 | 70  | 0.047                  | 4.5              | 9.5    | 7.2    | 5.0              | 100          | 32,000                                  | 79GC2470(1)40(2)      | R79GC2470(1)40(2)  |
| 160 | 70  | 0.056                  | 4.5              | 9.5    | 7.2    | 5.0              | 100          | 32,000                                  | 79GC2560(1)40(2)      | R79GC2560(1)40(2)  |
| 160 | 70  | 0.068                  | 4.5              | 9.5    | 7.2    | 5.0              | 100          | 32,000                                  | 79GC2680(1)40(2)      | R79GC2680(1)40(2)  |
| 160 | 70  | 0.082                  | 5.0              | 10.0   | 7.2    | 5.0              | 100          | 32,000                                  | 79GC2820(1)40(2)      | R79GC2820(1)40(2)  |
| 160 | 70  | 0.10                   | 5.0              | 10.0   | 7.2    | 5.0              | 100          | 32,000                                  | 79GC3100(1)40(2)      | R79GC3100(1)40(2)  |
| 160 | 70  | 0.12                   | 6.0              | 11.0   | 7.2    | 5.0              | 100          | 32,000                                  | 79GC3120(1)40(2)      | R79GC3120(1)40(2)  |
| 160 | 70  | 0.15                   | 6.0              | 11.0   | 7.2    | 5.0              | 100          | 32,000                                  | 79GC3150(1)40(2)      | R79GC3150(1)40(2)  |
| 160 | 70  | 0.18                   | 7.2              | 13.0   | 7.2    | 5.0              | 100          | 32,000                                  | 79GC3180(1)40(2)      | R79GC3180(1)40(2)  |
| 160 | 70  | 0.22                   | 7.2              | 13.0   | 7.2    | 5.0              | 100          | 32,000                                  | 79GC3220(1)40(2)      | R79GC3220(1)40(2)  |
| 250 | 160 | 0.012                  | 3.5              | 7.5    | 7.2    | 5.0              | 250          | 125,000                                 | 79IC2120(1)45(2)      | R79IC2120(1)45(2)  |
| 250 | 160 | 0.015                  | 3.5              | 7.5    | 7.2    | 5.0              | 250          | 125,000                                 | 79IC2150(1)45(2)      | R79IC2150(1)45(2)  |
| 250 | 160 | 0.018                  | 3.5              | 7.5    | 7.2    | 5.0              | 250          | 125,000                                 | 79IC2180(1)45(2)      | R79IC2180(1)45(2)  |
| 250 | 160 | 0.022                  | 3.5              | 7.5    | 7.2    | 5.0              | 250          | 125,000                                 | 79IC2220(1)45(2)      | R79IC2220(1)45(2)  |
| 250 | 160 | 0.027                  | 3.5              | 7.5    | 7.2    | 5.0              | 250          | 125,000                                 | 79IC2270(1)45(2)      | R79IC2270(1)45(2)  |
| 250 | 160 | 0.033                  | 3.5              | 7.5    | 7.2    | 5.0              | 250          | 125,000                                 | 79IC2330(1)45(2)      | R79IC2330(1)45(2)  |
| 250 | 160 | 0.039                  | 4.5              | 9.5    | 7.2    | 5.0              | 250          | 125,000                                 | 79IC2390(1)40(2)      | R79IC2390(1)40(2)  |
| 250 | 160 | 0.047                  | 4.5              | 9.5    | 7.2    | 5.0              | 250          | 125,000                                 | 79IC2470(1)40(2)      | R79IC2470(1)40(2)  |
| 250 | 160 | 0.056                  | 4.5              | 9.5    | 7.2    | 5.0              | 250          | 125,000                                 | 79IC2560(1)40(2)      | R79IC2560(1)40(2)  |
| 250 | 160 | 0.068                  | 5.0              | 10.0   | 7.2    | 5.0              | 250          | 125,000                                 | 79IC2680(1)40(2)      | R79IC2680(1)40(2)  |
| 250 | 160 | 0.082                  | 6.0              | 11.0   | 7.2    | 5.0              | 250          | 125,000                                 | 79IC2820(1)40(2)      | R79IC2820(1)40(2)  |
| 250 | 160 | 0.10                   | 6.0              | 11.0   | 7.2    | 5.0              | 250          | 125,000                                 | 79IC3100(1)40(2)      | R79IC3100(1)40(2)  |
| 250 | 160 | 0.12                   | 7.2              | 13.0   | 7.2    | 5.0              | 250          | 125,000                                 | 79IC3120(1)40(2)      | R79IC3120(1)40(2)  |
| 250 | 160 | 0.15                   | 7.2              | 13.0   | 7.2    | 5.0              | 250          | 125,000                                 | 79IC3150(1)40(2)      | R79IC3150(1)40(2)  |
| 400 | 200 | 0.0039                 | 3.5              | 7.5    | 7.2    | 5.0              | 400          | 320,000                                 | 79MC1390(1)40(2)      | R79MC1390(1)40(2)  |
| 400 | 200 | 0.0047                 | 3.5              | 7.5    | 7.2    | 5.0              | 400          | 320,000                                 | 79MC1470(1)40(2)      | R79MC1470(1)40(2)  |
| 400 | 200 | 0.0056                 | 3.5              | 7.5    | 7.2    | 5.0              | 400          | 320,000                                 | 79MC1560(1)40(2)      | R79MC1560(1)40(2)  |
| 400 | 200 | 0.0068                 | 3.5              | 7.5    | 7.2    | 5.0              | 400          | 320,000                                 | 79MC1680(1)40(2)      | R79MC1680(1)40(2)  |
| 400 | 200 | 0.0082                 | 3.5              | 7.5    | 7.2    | 5.0              | 400          | 320,000                                 | 79MC1820(1)40(2)      | R79MC1820(1)40(2)  |
| 400 | 200 | 0.010                  | 3.5              | 7.5    | 7.2    | 5.0              | 400          | 320,000                                 | 79MC2100(1)40(2)      | R79MC2100(1)40(2)  |
| 400 | 200 | 0.012                  | 4.5              | 9.5    | 7.2    | 5.0              | 400          | 320,000                                 | 79MC2120(1)40(2)      | R79MC2120(1)40(2)  |
| 400 | 200 | 0.015                  | 4.5              | 9.5    | 7.2    | 5.0              | 400          | 320,000                                 | 79MC2150(1)40(2)      | R79MC2150(1)40(2)  |
| 400 | 200 | 0.018                  | 5.0              | 10.0   | 7.2    | 5.0              | 400          | 320,000                                 | 79MC2180(1)40(2)      | R79MC2180(1)40(2)  |
| 400 | 200 | 0.022                  | 5.0              | 10.0   | 7.2    | 5.0              | 400          | 320,000                                 | 79MC2220(1)40(2)      | R79MC2220(1)40(2)  |
| 400 | 200 | 0.027                  | 6.0              | 11.0   | 7.2    | 5.0              | 400          | 320,000                                 | 79MC2270(1)40(2)      | R79MC2270(1)40(2)  |
| 400 | 200 | 0.033                  | 6.0              | 11.0   | 7.2    | 5.0              | 400          | 320,000                                 | 79MC2330(1)40(2)      | R79MC2330(1)40(2)  |
| 400 | 200 | 0.039                  | 7.2              | 13.0   | 7.2    | 5.0              | 400          | 320,000                                 | 79MC2390(1)40(2)      | R79MC2390(1)40(2)  |
| 400 | 200 | 0.047                  | 7.2              | 13.0   | 7.2    | 5.0              | 400          | 320,000                                 | 79MC2470(1)40(2)      | R79MC2470(1)40(2)  |
| 630 | 220 | 0.0010                 | 3.5              | 7.5    | 7.2    | 5.0              | 500          | 630,000                                 | 79PC1100(1)40(2)      | R79PC1100(1)40(2)  |
| 630 | 220 | 0.0012                 | 3.5              | 7.5    | 7.2    | 5.0              | 500          | 630,000                                 | 79PC1120(1)40(2)      | R79PC1120(1)40(2)  |
| 630 | 220 | 0.0015                 | 3.5              | 7.5    | 7.2    | 5.0              | 500          | 630,000                                 | 79PC1150(1)40(2)      | R79PC1150(1)40(2)  |
| 630 | 220 | 0.0018                 | 3.5              | 7.5    | 7.2    | 5.0              | 500          | 630,000                                 | 79PC1180(1)40(2)      | R79PC1180(1)40(2)  |
| 630 | 220 | 0.0022                 | 3.5              | 7.5    | 7.2    | 5.0              | 500          | 630,000                                 | 79PC1220(1)40(2)      | R79PC1220(1)40(2)  |
| 630 | 220 | 0.0027                 | 3.5              | 7.5    | 7.2    | 5.0              | 500          | 630,000                                 | 79PC1270(1)40(2)      | R79PC1270(1)40(2)  |
| 630 | 220 | 0.0033                 | 3.5              | 7.5    | 7.2    | 5.0              | 500          | 630,000                                 | 79PC1330(1)40(2)      | R79PC1330(1)40(2)  |
| 630 | 220 | 0.0039                 | 4.5              | 9.5    | 7.2    | 5.0              | 600          | 756,000                                 | 79PC1390(1)40(2)      | R79PC1390(1)40(2)  |
| 630 | 220 | 0.0047                 | 4.5              | 9.5    | 7.2    | 5.0              | 600          | 756,000                                 | 79PC1470(1)40(2)      | R79PC1470(1)40(2)  |
| 630 | 220 | 0.0056                 | 4.5              | 9.5    | 7.2    | 5.0              | 600          | 756,000                                 | 79PC1560(1)40(2)      | R79PC1560(1)40(2)  |
| 630 | 220 | 0.0068                 | 5.0              | 10.0   | 7.2    | 5.0              | 600          | 756,000                                 | 79PC1680(1)40(2)      | R79PC1680(1)40(2)  |
| 630 | 220 | 0.0082                 | 5.0              | 10.0   | 7.2    | 5.0              | 600          | 756,000                                 | 79PC1820(1)40(2)      | R79PC1820(1)40(2)  |
| 630 | 220 | 0.010                  | 6.0              | 11.0   | 7.2    | 5.0              | 600          | 756,000                                 | 79PC2100(1)40(2)      | R79PC2100(1)40(2)  |
| 630 | 220 | 0.012                  | 6.0              | 11.0   | 7.2    | 5.0              | 600          | 756,000                                 | 79PC2120(1)40(2)      | R79PC2120(1)40(2)  |
| 630 | 220 | 0.015                  | 7.2              | 13.0   | 7.2    | 5.0              | 600          | 756,000                                 | 79PC2150(1)40(2)      | R79PC2150(1)40(2)  |
| 630 | 220 | 0.018                  | 7.2              | 13.0   | 7.2    | 5.0              | 600          | 756,000                                 | 79PC2180(1)40(2)      | R79PC2180(1)40(2)  |
| VDC | VAC | Capacitance Value (µF) | B (mm)           | H (mm) | L (mm) | Lead Spacing (p) | dV/dt (V/µs) | Max K <sub>0</sub> (V <sup>2</sup> /µs) | New KEMET Part Number | Legacy Part Number |

(1) Insert lead and packaging code. See Ordering Options Table for available options.

(2) J = 5%, K = 10%, M = 20%



## Soldering Process


The implementation of the RoHS directive has resulted in the selection of SnAgCu (SAC) alloys or SnCu alloys as primary solder. This has increased the liquidus temperature from that of 183°C for SnPb eutectic alloy to 217 – 221°C for the new alloys. As a result, the heat stress to the components, even in wave soldering, has increased considerably due to higher pre-heat and wave temperatures. Polypropylene capacitors are especially sensitive to heat (the melting point of polypropylene is 160 – 170°C). Wave soldering can be destructive, especially for mechanically small polypropylene capacitors (with lead spacing of 5 mm to 15 mm), and great care has to be taken during soldering. The recommended solder profiles from KEMET should be used. Please consult KEMET with any questions. In general, the wave soldering curve from IEC Publication 61760-1 Edition 2 serves as a solid guideline for successful soldering. Please see Figure 1.

Reflow soldering is not recommended for through-hole film capacitors. Exposing capacitors to a soldering profile in excess of the above the recommended limits may result to degradation or permanent damage to the capacitors.

Do not place the polypropylene capacitor through an adhesive curing oven to cure resin for surface mount components. Insert through-hole parts after the curing of surface mount parts. Consult KEMET to discuss the actual temperature profile in the oven, if through-hole components must pass through the adhesive curing process. A maximum two soldering cycles is recommended. Please allow time for the capacitor surface temperature to return to a normal temperature before the second soldering cycle.


### Manual Soldering Recommendations

Following is the recommendation for manual soldering with a soldering iron.



The soldering iron tip temperature should be set at 350°C (+10°C maximum) with the soldering duration not to exceed more than 3 seconds.

### Wave Soldering Recommendations



## Soldering Process cont'd


### Wave Soldering Recommendations cont'd

1. The table indicates the maximum set-up temperature of the soldering process  
Figure 1

| Dielectric Film Material | Maximum Preheat Temperature |                         |                         | Maximum Peak Soldering Temperature |                         |
|--------------------------|-----------------------------|-------------------------|-------------------------|------------------------------------|-------------------------|
|                          | Capacitor Pitch ≤ 10 mm     | Capacitor Pitch = 15 mm | Capacitor Pitch > 15 mm | Capacitor Pitch ≤ 15 mm            | Capacitor Pitch > 15 mm |
| Polyester                | 130°C                       | 130°C                   | 130°C                   | 270°C                              | 270°C                   |
| Polypropylene            | 100°C                       | 110°C                   | 130°C                   | 260°C                              | 270°C                   |
| Paper                    | 130°C                       | 130°C                   | 140°C                   | 270°C                              | 270°C                   |
| Polyphenylene Sulphide   | 150°C                       | 150°C                   | 160°C                   | 270°C                              | 270°C                   |

2. The maximum temperature measured inside the capacitor:  
Set the temperature so that inside the element the maximum temperature is below the limit:

| Dielectric Film Material | Maximum temperature measured inside the element |
|--------------------------|---|
| Polyester                | 160°C   |
| Polypropylene            | 110°C   |
| Paper                    | 160°C   |
| Polyphenylene sulphide   | 160°C   |



*Temperature monitored inside the capacitor.*


### Selective Soldering Recommendations

Selective dip soldering is a variation of reflow soldering. In this method, the printed circuit board with through-hole components to be soldered is preheated and transported over the solder bath as in normal flow soldering without touching the solder. When the board is over the bath, it is stopped and pre-designed solder pots are lifted from the bath with molten solder only at the places of the selected components, and pressed against the lower surface of the board to solder the components.


The temperature profile for selective soldering is similar to the double wave flow soldering outlined in this document, **however, instead of two baths, there is only one bath with a time from 3 to 10 seconds.** In selective soldering, the risk of overheating is greater than in double wave flow soldering, and great care must be taken so that the parts are not overheated.

## Construction


### Wound



### Winding Scheme




## Marking



## Packaging Quantities

| Lead Spacing | Thickness (mm) | Height (mm) | Length (mm) | Bulk Short Leads | Bulk Long Leads | Standard Reel<br>Ø 355 mm | Large Reel<br>Ø 500 mm | Ammo Taped |
|--------------|----------------|-------------|-------------|------------------|-----------------|---------------------------|------------------------|------------|
| 5            | 3.5            | 7.5         | 7.2         | 2,000            | 3,000           | 1,800                     |                        | 2,500      |
|              | 4.5            | 9.5         | 7.2         | 1,500            | 2,000           | 1,400                     |                        | 1,900      |
|              | 5.0            | 10          | 7.2         | 1,000            | 1,500           | 1,200                     |                        | 1,700      |
|              | 6.0            | 11          | 7.2         | 2,000            | 1,000           | 1,000                     |                        | 1,400      |
|              | 7.2            | 13          | 7.2         | 1,500            | 750             | 800                       |                        | 1,150      |

## Lead Taping & Packaging (IEC 60286-2)



## Taping Specification

| Description                          | Symbol           | Dimensions (mm) |           |
|--------------------------------------|------------------|-----------------|-----------|
|                                      |                  | Lead Spacing    | Tolerance |
|                                      |                  | 5               |           |
| Lead wire diameter                   | d                | 0.5             | ±0.05     |
| Taping lead space                    | P                | 12.7            | ±1        |
| Feed hole lead space                 | P <sub>0</sub>   | 12.7            | ±0.2**    |
| Centering of the lead wire           | P <sub>1</sub>   | 3.85            | ±0.7      |
| Centering of the body                | P <sub>2</sub>   | 6.35            | ±1.3      |
| Lead spacing                         | F                | 5               | +0.6/-0.1 |
| Component alignment                  | Dh               | 0               | ±2        |
| Height of component from tape center | H <sub>0</sub> * | 18.5            | ±0.5      |
| Carrier tape width                   | W                | 18              | +1/-0.5   |
| Hold down tape width                 | W <sub>0</sub>   | 6               | Minimum   |
| Hole position                        | W <sub>1</sub>   | 9               | ±0.5      |
| Hold down tape position              | W <sub>2</sub>   | 3               | Maximum   |
| Feed hole diameter                   | D <sub>0</sub>   | 4               | ±0.2      |
| Total Tape thickness                 | t                | 0.7             | ±0.2      |

\*H<sub>0</sub> = 16.5 mm is available upon request.


\*\*Maximum 1 mm on 20 lead spacing.

## Lead Taping & Packaging (IEC 60286–2) cont'd

### Ammo Specifications


| Dimensions (mm) |     |    |
|-----------------|-----|----|
| H               | W   | T  |
| 360*            | 340 | 59 |

\* Lower dimension available upon request (Maximum 295 mm)



### Reel Specifications

| Dimensions (mm) |    |            |
|-----------------|----|------------|
| D               | H  | W          |
| 355             | 30 | 55 Maximum |



### Manufacturing Date Code (IEC–60062)

| Y = Year, Z = Month |      |           |      |
|---------------------|------|-----------|------|
| Year                | Code | Month     | Code |
| 2010                | A    | January   | 1    |
| 2011                | B    | February  | 2    |
| 2012                | C    | March     | 3    |
| 2013                | D    | April     | 4    |
| 2014                | E    | May       | 5    |
| 2015                | F    | June      | 6    |
| 2016                | H    | July      | 7    |
| 2017                | J    | August    | 8    |
| 2018                | K    | September | 9    |
| 2019                | L    | October   | 0    |
| 2020                | M    | November  | N    |
| 2021                | N    | December  | D    |
| 2022                | P    |           |      |
| 2023                | R    |           |      |
| 2024                | S    |           |      |
| 2025                | T    |           |      |
| 2026                | U    |           |      |
| 2027                | V    |           |      |
| 2028                | W    |           |      |
| 2029                | X    |           |      |
| 2030                | A    |           |      |

## KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit [www.kemet.com/sales](http://www.kemet.com/sales).

---

### Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

*KEMET is a registered trademark of KEMET Electronics Corporation.*