




Energy & Power > Power Systems Connectors > Mechanical Connectors > High Voltage Flexible Cable Connectors



Mechanical Connector Product Type: **Connector**

Installation Technology: **Bolted**

Voltage Class: **≤ 550 kV**

Compatible Conductor Material: **Aluminum Alloy**

Conductor Type: **Flexible Conductor**

[All High Voltage Flexible Cable Connectors \(859\)](#)

Features

Product Type Features

Installation Technology	Bolted
-------------------------	--------

Configuration Features

Visual Inspection	No
Number of Bolts	4

Electrical Characteristics

Voltage Class	≤ 550 kV
---------------	----------

Body Features

Compatible Conductor Material	Aluminum Alloy
Conductor Type	Flexible Conductor
Primary Product Material	Aluminum
Blocked	Yes

Dimensions

Bolt Head Size (Across Flats)	17 mm
Compatible Conductor Cross-Section Range	400 – 630 mm²

Operation/Application

--	--



Power Component Application Type	Indoor Use, Outdoor Use
Mechanical Connector Product Type	Connector

Industry Standards

NEMA Spacing (2-Hole)	Yes
Compatible With Approved Standards Products	ANSI/NEMA CC1-2009, IEC 62271-1

Product Availability

Product Availability	Worldwide
----------------------	-----------

Other

Conductor Gauge Type	AAC/AAAC, ACSR, AWG
----------------------	---------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.



Compatible Parts



TE Part # CAT-SIMAFLEX
High Voltage Flexible Cable
Connectors

Also in the Series | SIMAFLEX



Mechanical Connectors(862)

Customers Also Bought



TE Part #2331111-1
5 CT 82 S265 S305

Documents

Product Drawings

5 CT 82 S265

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2331108-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2331108-1_A.3d_igs.zip

English



Customer View Model

[ENG_CVM_CVM_2331108-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SIMAFLEX CONNECTORS \(DDS\)](#)

English

[SIMAFLEX SUBSTATION CONNECTOR SYSTEM](#)

English

Product Specifications

[Product Specification](#)

English