




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Right Angle**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Number of Rows: **2**

Features

Product Type Features

Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Loaded Positions	2
Number of Power Positions	2
PCB Mount Orientation	Right Angle
Number of Positions	2
Number of Rows	2

Electrical Characteristics



Operating Voltage	600 VAC
Body Features	
Primary Product Color	Natural
Contact Features	
Contact Underplating Material	Nickel
Contact Underplating Material Thickness	.381 µm[15 µin]
Contact Mating Area Plating Material Thickness	2.03 µm[80 µin]
PCB Contact Termination Area Plating Material Thickness	2.03 µm[80 µin]
Contact Layout	Matrix
Contact Base Material	Brass Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Tab
Contact Current Rating (Max)	9 A
Termination Features	
Termination Post & Tail Length	3.6 mm[.141 in]
Termination Method to PCB	Through Hole - Solder
Mechanical Attachment	
Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Keyed
PCB Mount Alignment Type	Screw Mount
PCB Mount Retention	Without
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With
Housing Features	
Housing Material	Nylon
Centerline (Pitch)	4.2 mm[.165 in]
Dimensions	
Row-to-Row Spacing	4.2 mm[.165 in]
Connector Width	12.8 mm[.5 in]



PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	9.8 mm[.386 in]
Connector Length	5.4 mm[.213 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	260
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1969612-2
2P FH PLUG VAL-U-LOK V0




TE Part # 1586019-2
2P RCPT VAL-U-LOK V0




TE Part # 1969613-2
2P PM PLUG VAL-U-LOK V0


Customers Also Bought



TE Part #3-5177986-5
0.8FH,P08H.5,120,08/Sn,TR,SC




TE Part #1586042-2
2P VAL-U-LOK R/A HDR V0



TE Part #4-2176312-3
RP 1E 0.1W 34K 0.1% 25PPM 1K RL




TE Part #5788793-1
09 HTMSFL PLUG RA 318 (SL,BL)




TE Part #4-2176421-1
TLRP 2512 2.0W R200 1% 25PPM 4K RL




TE Part #2108609-5
3.0H SPRING FINGER WITH EMBOSS



TE Part #5-146247-1
16 MODII HDR DRRA 3/4 SHRD LF



TE Part #1586044-6
6P VAL-U-LOK R/A HDR SCR MT V0



TE Part #9-215079-0
MICRO-MATCH FOB.20P



TE Part #T4140012051-000
M12,REAR MOUNTING,MALE,A CODE,5P



Documents

Product Drawings

2P VAL-U-LOK R/A HDR SCR MT V0

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1586044-2_A_c-1586044-2-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1586044-2_A_c-1586044-2-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1586044-2_A_c-1586044-2-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English

UL Report

English