



Safety Data Sheet according to (EC) No 1907/2006 - ISO 11014-1

Page 1 of 5

Loctite 268

sds no. : 153641
V002.0

Revision: 17.05.2010
printing date: 21.05.2010

CP1026 v1.2 RS 480-4086

RS REACH revision date 01/06/10

1. Identification of the substance/preparation and of the company/undertaking

Trade name:

Loctite 268

Intended use:

Threadlocker

Company name:

Henkel Limited
Technologies House
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (0)1442 278000
Fax-no.: +44 (0)1442 278071

Supplied by:
RS Components Ltd,
Birchington Road, Corby, Northants, NN17 9RS.
Tel: +44 (0) 1536 402888 (8am to 8pm)
Email: technical.help@rs-components.com

E-mail address of person responsible for Safety Data Sheet:

ua-productsafety.uk@uk.henkel.com

Emergency information:

24 Hours Emergency Tel: +44 (0)1442 278497

2. Hazards identification

R36/37/38 Irritating to eyes, respiratory system and skin.

3. Composition / information on ingredients

General chemical description:

Threadlocker Stick

Declaration of ingredients according to (EC) No 1907/2006:

Hazardous components CAS-No.	EINECS ELINCS	content	Classification
Cumene hydroperoxide 80-15-9	201-254-7	0,1 - 1 %	T - Toxic; R23 Xn - Harmful; R21/22, R48/20/22 O - Oxidizing; R7 C - Corrosive; R34 N - Dangerous for the environment; R51, R53
Cumene 98-82-8	202-704-5	0,1 - 1 %	R10 Xn - Harmful; R65 Xi - Irritant; R37 N - Dangerous for the environment; R51, R53
N,N-dimethyl-o-toluidine 609-72-3	210-199-8	0,1 - 1 %	R52, R53 T - Toxic; R23/24/25 R33
Bisphenol A -methacrylatoethyl ether 24448-20-2	246-263-7	25 - 50 %	No classification required.

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.

Substances without classification may have community workplace exposure limits available.

4. First aid measures

Inhalation:

Should not be a problem as product is of low volatility. However, if feeling unwell remove patient to fresh air.

Skin contact:

Rinse with running water and soap.
Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.
Seek medical advice.

5. Fire fighting measures

Suitable extinguishing media:

Carbon dioxide, foam, powder

Special protection equipment for firefighters:

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

6. Accidental release measures

Environmental precautions:

Waste disposal with the approval of the responsible local authority.

7. Handling and storage

Handling:

Use only in well-ventilated areas.
Avoid skin and eye contact.
Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

Storage:

Store in a cool, well-ventilated place.

8. Exposure controls / personal protection

Components with specific control parameters for workplace:

Valid for

Great Britain

Basis

UK EH40 WELs

Ingredient	ppm	mg/m3	Type	Category	Remarks
CUMENE 98-82-8	25	125	Time Weighted Average (TWA).		EH40 WEL
CUMENE 98-82-8	50	250	Short Term Exposure Limit (STEL):		EH40 WEL
CUMENE 98-82-8			Skin designation:	Can be absorbed through the skin.	EH40 WEL
CUMENE 98-82-8			Skin designation:	Can be absorbed through the skin.	ECLTV
CUMENE 98-82-8	50	250	Short Term Exposure Limit (STEL):	Indicative	ECLTV
CUMENE 98-82-8	20	100	Time Weighted Average (TWA).	Indicative	ECLTV

Respiratory protection:

Use only in well-ventilated areas.

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (IIR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (IIR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Skin protection:

Wear suitable protective clothing.

General protection and hygiene measures:

Good industrial hygiene practices should be observed.

9. Physical and chemical properties

General characteristics:

Appearance	solid material wax Red
Odor:	Mild

Phys./chem. properties:

pH-value	not applicable
Boiling point	> 149 °C (> 300.2 °F)
Flash point	Not applicable
Vapor pressure (20 °C (68 °F))	< 6,67 mbar
Density ()	1,07 g/cm3

Solubility (qualitative) (Solvent: Water)	Slight
Solubility (qualitative) (Solvent: Acetone)	Not applicable
VOC content (1999/13/EC)	< 3 %

10. Stability and reactivity

Conditions to avoid:

Stable under normal conditions of storage and use.

11. Toxicological information

Inhalative toxicity:

Irritating to respiratory system

Skin irritation:

Irritating to the skin.

Eye irritation:

Irritating to eyes.

12. Ecological information

Ecotoxicity:

Hazardous components CAS-No.	Species	Exposure time	Value type	Value
Cumene hydroperoxide 80-15-9	Ide, silver or golden orfe (Leuciscus idus) Water flea (Daphnia magna)	48 h 24 h	LC 50 EC 50	14 mg/l 7 mg/l
Cumene hydroperoxide 80-15-9				
Cumene 98-82-8	Trout family (Salmonidae)	96 h	LC 50	4,8 mg/l
N,N-dimethyl-o-toluidine 609-72-3	Fathead minnow (Pimephales promelas)	96 h	LC 50	46 mg/l

General ecological information:

Do not empty into drains / surface water / ground water.

In the cured state contribution of this product to Environmental Hazards is insignificant in comparison to articles in which it is used.

13. Disposal considerations

Product disposal:

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Waste code(EWC):

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

14. Transport information

General information:

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

15. Regulations - classification and identification**Indication of danger:**

Xi - Irritant

**Risk phrases:**

R36/37/38 Irritating to eyes, respiratory system and skin.

Safety phrases:

S23 Do not breathe vapour.

S24/25 Avoid contact with skin and eyes.

S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

16. Other information

The labelling of the product is indicated in Section 15. The full text of the R-phrases indicated by codes in this safety data sheet are as follows:

R10 Flammable.

R21/22 Harmful in contact with skin and if swallowed.

R23 Toxic by inhalation.

R23/24/25 Toxic by inhalation, in contact with skin and if swallowed.

R33 Danger of cumulative effects.

R34 Causes burns.

R37 Irritating to respiratory system.

R48/20/22 Harmful: danger of serious damage to health by prolonged exposure through inhalation and if swallowed.

R51 Toxic to aquatic organisms.

R52 Harmful to aquatic organisms.

R53 May cause long-term adverse effects in the aquatic environment.

R65 Harmful: may cause lung damage if swallowed.

R7 May cause fire.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

This safety data sheet was prepared in accordance with Council Directive 67/548/EEC and its subsequent amendments, and Commission Directive 1999/45/EC.