

General Information

Extended Product Type:	M2.5/6.2G.2G.1
Product ID:	1SNA115267R2600
EAN:	3472591152678
Catalog Description:	M2.5/6.2G.2G Specific Terminal Blocks Feed-through Grey
Long Description:	Quick-connect feed-through blocks

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Solution Series

Ordering

EAN:	3472591152678
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	6 mm
Product Net Height:	44.5 mm
Product Net Depth:	40.5 mm
Product Net Weight:	8 g

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	61 mm
Package Level 1 Height:	47 mm
Package Level 1 Length:	220 mm
Package Level 1 Gross Weight:	0.4 kg
Package Level 1 EAN:	3472591152678
Package Level 2 Units:	1000 piece
Package Level 3 Units:	48000 piece
Product Packing Type:	Box

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Flammability According to UL94:	V2

Additional Information

Ambient Temperature:	-5 ... +40 °C
Color:	Grey
Connection Type:	Quick-connect
Dielectric Test Voltage:	3500 V
Function:	Feed-through
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Maximum Rated Connecting Capacity:	Tabs 6.3*0.8 2.5 mm ² Tabs 2.8*0.8 1.5 mm ²
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Levels:	1
Pollution Degree:	2
Product Main Type:	M2.5/6.2G.2G
Product Name:	Terminal Block
Rated Cross-Section:	2.5 mm ²
Rated Impulse Withstand Voltage (U _{imp}):	6000 V
Rated Voltage (U _r):	630 V
Spacing:	6 mm
Sub-Function:	2 clips

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SNC160001C0205_CHC2
Declaration of Conformity - CE:	1SND225003C1007
EAC Certificate:	1SND161009A1100
RoHS Information:	1SND230021F0201

Classifications

ETIM 4.0:	EC000897 - Feed-through terminal block
ETIM 5.0:	EC000897 - Feed-through terminal block
Object Classification Code:	X

