



Part Number : [192050004](#)
Product Description : VersaKrimp Parallel Splice for
8 AWG Wire
Series Number : 19205
Status : Active
Product Category : Splices
Engineering Number : D-355




Documents & Resources

Drawings
[192050004 sd.pdf](#)
Specifications
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19205
Description	VersaKrimp Parallel Splice for 8 AWG Wire
Product Name	Parallel,VersaKrimp
UPC	800755060843

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.887/g
Packaging Type	Bag
Wire Size (AWG)	8

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper,	<u>192860117</u>

Die Set Required, For Insulated and Non-Insulated Terminals and Splices	
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900001</u>
Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals	<u>192940008</u>
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
RHT1080 Hand Crimp Tool	<u>640034400</u>
Square "DIN" style dies for 8 AWG	<u>640037670</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640074400</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>