

Previously known as: MICROGARD® 2000 STANDARD - Model 162

### Superior, breathable microporous laminate chemical-protective suit, suitable for diverse applications.

- **Specialized protection:** The AlphaTec® 2000 STANDARD Bound - Model 162 features low-linting fabric, for lower cross contamination risks, and offers light chemical resistance\*, withstanding low-concentration liquid chemicals and liquid and particulate biological hazards
- **Advanced breathability:** Microporous polyethylene laminate nonwoven fabric makes this protective outer garment water vapor-permeable, limiting heat stress risks
- **Enhanced fit and features:** An optimized fit and finger loops make for safer, more comfortable wear, while a pass-thru device facilitates fall arrest equipment, and an elasticated hood and two-way front zipper with resealable storm flap make for convenient use
- **Reduced surface defect risks:** Being silicone-free, this protective suit is perfectly suitable for spray-painting applications
- **Assured antistatic capabilities:** It also meets EN 1149-5 antistatic standards

\*CE Category III Type 5/6 protection



## Industries

- Life Sciences
- Automotive
- Metal fabrication
- Food Processing
- Defense
- Agriculture
- Automotive Aftermarket
- Chemical
- Emergency Medical Services
- Machinery and Equipment
- Oil and gas
- Utilities
- Nuclear

## Applications

- Clean room cleaning and preparing
- Body painting including surface inspection
- Production line support & maintenance
- Cleaning of plant and machines
- Maintenance of plant and machines
- Veterinary Services


## KEY FEATURES & BENEFITS

- **Protective barrier:** Low-concentration liquid chemicals, liquid and particulate biological hazards
- **Microporous laminate fabric:** Offers protection against heat stress
- **Pass-thru device:** Suitable for use with fall arrest equipment

## Material Diagram



## Seam Diagram



Performance Standards



Product Information

| Product Information |   |
|---------------------|---|
| Available Sizes     | S, M, L, XL, 2XL, 3XL, 4XL, 5XL   |
| Color               | White   |
| Country Of Origin   | China   |
| Models Available    | 111, 102, 103, 113, 122   |
| Packaging Overview  | Individually Packed   |
| Product Material    | Microporous polyethylene Laminate non-woven                                     |
| Product Reference   | 2000 STANDARD - Model 162   |
| Standards Overview  | CE CATEGORY III (Type 5-B, Type 6-B, EN 1073-2, EN 14126, DIN 32781, EN 1149-5) |
| Seam Type           | Bound   |
| Shelf Life          | 5 years   |
| Style Number        | W20B162   |

Suit components & accessories

| Suit Components and Accessories |  |
|---------------------------------|--|
| Design Features                 | Pass-thru device for use with fall arrest equipment, 3-piece hood, 2-way front zipper with re-sealable storm flap, finger loops. Elasticated hood, waist, wrists and ankles. |

For additional in formation visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00

**North America Region**  
Ansell Healthcare Products LLC  
T: +1 800 800 0444

**Australia**  
Ansell Limited  
T: +61 1800 337 041

**Asia Pacific Region**  
Ansell Global Trading Center  
T: +603 8310 6688

**Latin America & Caribbean Region**  
Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

