



Main

Range of product	Harmony XVC6
Product or component type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	4 illuminated units
Sound signalling	Buzzer
Mounting diameter	60 mm
Component name	XVC
Light source	Red LED steady or flashing Orange LED steady or flashing Green LED steady or flashing Blue LED steady or flashing
[Us] rated supply voltage	100...240 V
Supply circuit type	AC
Noise level	70...85 dB (continuous or intermittent tone) at 1 m

Complementary

Material	PBT + ABS (UL94-V0) (top cover) ABS (acrylonitrile butadiene-styrene) (base unit) Polycarbonate (illuminated unit)
Product mounting	On base
Cable cross section	0.33 mm ² 0.83 mm ²
AWG gauge	18 22
Cable length	750 mm 850 mm
Marking	CE
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	100 mA
Fundamental frequency	2.23 kHz
Flashing frequency	1 Hz
Product weight	0.65 kg
Height	352 mm



Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Class of protection against electric shock	Class I conforming to EN/IEC 61140
IP degree of protection	IP54 in flat surface installation conforming to EN/IEC 60529

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0808 - Schneider Electric declaration of conformity
Product end of life instructions	Need no specific recycling operations

Dimensions

$$\frac{\text{mm}}{\text{in.}}$$


No. of illuminated units	b (mm)	b (in.)
1 stage	232	9.13
2 stages	272	10.71
3 stages	312	12.28
4 stages	352	13.86
5 stages	392	15.43

Pre-assembled and Pre-wired Tower Light

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out

