# **Product data sheet**

Specifications





# pressure switch XMLA 20 bar - fixed scale 1 threshold - 1 C/O

XMLA020B2S12

Main	
Range of product	Telemecanique Pressure sensors XM
Product or component type	Electromechanical pressure sensor
Pressure sensor type	Electromechanical pressure sensor
Device short name	XMLA
Pressure rating	20 bar
Controlled fluid	Air (0160 °C) Fresh water (0160 °C) Hydraulic oil (0160 °C)
Fluid connection type	G 1/4 (female) conforming to ISO 228
Electrical connection	Screw-clamps terminals, 1 x 0.52 x 2.5 mm <sup>2</sup>
AWG gauge	AWG 20AWG 14
Cable entry	Cable gland 713 mm
Contacts type and composition	1 C/O
Product specific application	•
Pressure switch type of operation	Detection of 1 single threshold
Electrical circuit type	Control circuit
Scale type	Fixed differential
Local display	With
Adjustable range of switching point on rising pressure	120 bar
Adjustable range of switching point on falling pressure	0.619 bar
Maximum permissible accidental pressure	45 bar
Destruction pressure	90 bar
Pressure actuator	Diaphragm
Materials in contact with fluid	Brass FPM, FKM
Enclosure material	Zinc alloy
[In] rated current	3 A, B300, AC-15 (Ue = 120 V) conforming to EN/IEC 60947-5-1 1.5 A, B300, AC-15 (Ue = 240 V) conforming to EN/IEC 60947-5-1 0.1 A, R300, DC-13 (Ue = 250 V) conforming to EN/IEC 60947-5-1

Complementary	
Natural differential at low setting	0.4 bar (+/- 0.2 bar)
Natural differential at high setting	1 bar (+/- 0.1 bar)
Maximum permissible pressure - per cycle	25 bar
Terminal block type	4 terminals
Maximum operating rate	120 cyc/mn
Repeat accuracy	2 %
[Ui] rated insulation voltage	300 V conforming to UL 508 500 V conforming to EN/IEC 60947-1 300 V conforming to CSA C22.2 No 14
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-1
Auxiliary contacts operation	Snap action
Contacts material	Silver contacts
Maximum resistance across terminals	25 mOhm conforming to IEC 255-7 category 3 25 mOhm conforming to NF C 93-050 method A
Short-circuit protection	10 A cartridge fuse, type gG (gl)
Mechanical durability	5000000 cycles
Setting	External
Height	113 mm
Depth	75 mm
Width	35 mm
Net weight	0.685 kg
Environment	
Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 CE UL 508
Product certifications	CCC LROS (Lloyds register of shipping) CSA BV EAC UL
Protective treatment	TC standard version
Ambient air temperature for operation	-2570 °C
Ambient air temperature for storage	-4070 °C

4 gn conforming to IEC 60068-2-6 (f = 30...500 Hz)

50 gn conforming to IEC 60068-2-27

Class I conforming to IEC 1140 Class I conforming to IEC 536 Class I conforming to NF C 20-030

IP66 conforming to EN/IEC 60529

Any position

class

Operating position

Vibration resistance

Electrical shock protection

IP degree of protection

Shock resistance

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	85.0 g
Package 1 Height	12.5 cm
Package 1 width	4.2 cm
Package 1 Length	8.2 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

### **Contractual warranty**


<del>_</del>	
14/	
Warranty	18 months

## **Product data sheet**

## XMLA020B2S12

**Dimensions Drawings** 

#### **Dimensions**



- 1 fluid entry, tapped G1/4 (BSP female) 1 electrical connections entry, tapped M20 x 1.5 2 elongated holes Ø 5.2 x 6.7
- (1) (2) Ø :

## **Product data sheet**

# XMLA020B2S12

Connections and Schema


### Wiring Diagram


#### **Terminal Model**




Performance Curves

#### **Operating Curves**







- Pressure Time
- (y) (x) (1) (2) PH: Adjustable value
  Non adjustable value
- High point Below point