

Sep.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case that the application demands a high level of reliability, such as automotive,
 please contact a company representative for further information.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	1 \triangleright -25 °C TO +105 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C
	VOLTAGE	_____	APPLICABLE CABLE	22 mm ² or AWG #4 OUTER DIAMETER : ϕ 12.4 max.
	CURRENT	2 \triangleright 94 A		
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
Δ				
REMARK		APPROVED	SU. OBARA	13.02.22
NOTE 1 \triangleright OPERATING TEMPERATURE RANGE INCLUDES THE TEMPERATURE RISE BY CURRENT CARRYING.		CHECKED	YH. YAMADA	13.02.22
2 \triangleright RATING CURRENT SHALL BE TESTED UNDER MATED CONDITION WITH AN APPLICABLE CONNECTOR.		DESIGNED	HS. KAWASHIMA	13.02.22
Unless otherwise specified, refer to JIS C 5402, IEC 60512.		DRAWN	KN. IKEHARA	13.02.22
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-118015-00	
HRS	SPECIFICATION SHEET	PART NO.	EF1-38-22	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL142-0006-7-00	Δ 1/1