



SDSHM127

HAMMERITE WAXOYL AEROSOL SAFETY DATA SHEET

Revision 04/2010

1. IDENTIFICATION OF THE PREPARATION AND COMPANY

PRODUCT NAME : Hammerite Waxoyl Aerosol

Supplied by : ICI Paints AkzoNobel, Wexham Road, Slough, Berkshire, SL2 5DS, U.K.

E-mail address : duluxtrade_advice@ici.com

Emergency Telephone : Slough +44 (0) 1753 550000

INTENDED USE

ICI Paints AkzoNobel's decorative products are intended for use in the decoration of buildings surfaces. Refer to product label for details of areas of use and methods of application.

Supplied by: RS Components Ltd, Birchington Road, Corby, Northants, NN17 9RS. Tel: +44 (0) 1536 402888 (8am to 8pm) Email: technical.help@rs-components.com
--

2. HAZARDS IDENTIFICATION

This product has been assessed under the CHIP Regulations and is classified as follows:

For BLACK:

Indication(s) of Danger

Extremely Flammable, Dangerous For The Environment, Harmful

Symbol Letter(s)

F+, N, Xn

Category(ies) of Danger

Extremely Flammable, Dangerous For The Environment, Carcinogenic: Category 3

For CLEAR:

Indication(s) of Danger

Extremely Flammable, Dangerous For The Environment

Symbol Letter(s)

F+, N

Category(ies) of Danger

Extremely Flammable, Dangerous For The Environment

Warning Label Phrases

For BLACK and CLEAR:

- R12 Extremely flammable.
- R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R66 Repeated exposure may cause skin dryness or cracking.
- P96 Pressurised container: protect from sunlight and do not expose to temperature exceeding 50 degrees C. Do not pierce or burn, even after use.
- P97 Do not spray on a naked flame or any incandescent material. Keep away from sources of ignition - No smoking. Keep out of the reach of children.

Plus for BLACK only:

- R40 Limited evidence of a carcinogenic effect.

Information on Occupational Exposure Limits is given in Section 8.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substances presenting a physico-chemical, health or environmental hazard within the meaning of the CHIP Regulations or which are assigned occupational exposure limits.

EC No.	CAS No.	HAZARDOUS INGREDIENTS	%	CLASSIFICATION	
265-185-4	64742-82-1	NAPHTHA (PETROLEUM), HYDRODESULFURIZED HEAVY	50-75	N, Xn	R10-51/53-65-66
200-827-9	74-98-6	PROPANE	10-25	F+	R12
203-448-7	106-97-8	BUTANE(CONT.<0.1%BUTADIENE)	2.5-10	F+	R12

200-857-2	75-28-5	ISOBUTANE	1.0-2.5	F+	R12
	68038-16-4	OLEYL IMIDAZOLINE DIOLEATE SALT	1.0-2.5	Xi	R36-38

Plus for BLACK only:

265-196-4	64742-93-4	PETROLEUM BITUMEN	<10	Xn	R40	Carc. Cat. 3
-----------	------------	-------------------	-----	----	-----	--------------

Note: The text for R phrase codes shown above (if any) is given in section 16.

Note: 'EC Number' if quoted is the EINECS or ELINCS number.

4. FIRST-AID MEASURES

In all cases of doubt, or where symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person.

INHALATION: Remove to fresh air, keep patient warm and at rest. If breathing is irregular or stopped administer artificial respiration. Give nothing by mouth. If unconscious place in the recovery position. Seek medical advice.

EYE CONTACT: Remove contact lenses. Irrigate copiously with clean, fresh water for at least 10 minutes, holding lids apart. Seek medical advice.

SKIN CONTACT: Remove contaminated clothing, wash skin thoroughly with soap and water, or use a proprietary skin cleanser. Do not use solvents or thinners. Seek medical advice if symptoms persist.

INGESTION: If accidentally swallowed, DO NOT INDUCE VOMITING. Keep at rest and obtain medical attention.

5. FIRE-FIGHTING MEASURES

Extinguishing media: Recommended - alcohol resistant foam, CO₂, powders.

Not to be used - waterjet.

Recommendations : Fire will produce dense black smoke. Exposure to decomposition products may cause a health hazard.

Fire fighters should wear self-contained breathing apparatus.

Closed containers exposed to fire should be cooled with water. Do not allow run-off from fire-fighting to enter drains or water-courses.

6. ACCIDENTAL RELEASE MEASURES

Exclude non-essential personnel.

Exclude sources of ignition and ventilate the area. Avoid breathing vapours. Refer to protective measures listed in section 8. Contain and collect spillage with non-combustible absorbent materials, eg sand, earth, vermiculite or diatomaceous earth, and place in container for disposal according to local regulations (see section 13). Do not allow to enter drains or watercourses. Clean preferably with a detergent; avoid use of solvents. If the product enters drains or sewers, immediately contact the local water company; in the case of contamination of streams, rivers or lakes, the relevant environment agency.

7. HANDLING AND STORAGE

HANDLING CONDITIONS: Vapours are heavier than air and may spread along floors. They may form explosive mixtures with air. Prevent the creation of flammable or explosive concentrations of vapour in air and avoid vapour concentrations higher than the occupational exposure limits. In addition, the product should only be used in areas from which all naked lights and other sources of ignition have been excluded. Electrical equipment should be protected by the appropriate standard. Keep the container tightly closed. Exclude sources of heat, sparks and open flame. Non-sparking tools should be used. Avoid skin and eye contact. Avoid the inhalation of vapour and mist. Smoking, eating and drinking should be prohibited in storage and use areas. For personal protective equipment see Section 8. Always keep in containers made of the same material as the supply container, or in containers that are compatible with the product. The accumulation of contaminated rags may result in spontaneous combustion. Good housekeeping standards and regular safe removal of waste materials will minimise the risks of spontaneous combustion and other fire hazards.

Preparations may charge electrostatically: always use earthing leads when transferring from one container to another. Operators should wear antistatic footwear and clothing, and floors should be of the conducting type.

STORAGE CONDITIONS: Observe the label precautions. Store in a cool, dry, well ventilated place away from sources of heat, ignition and direct sunlight. No smoking. Prevent unauthorised access. Containers which are opened should be properly resealed and kept upright to prevent leakage.

The Manual Handling Operations Regulations 1993 may apply to the handling of certain Paint Products. Products packed in containers of 5 litres and above will be marked with a guide weight; refer to these weights when carrying out an assessment.

The principles contained in the HSE guidance note Storage of Packaged Dangerous Substances, should be observed when storing this product. Store separately from oxidising agents, strongly alkaline and strongly acidic materials, amines, alcohols and water.

SPECIFIC USE(s): Where applicable refer to the product label and literature for the application and use instructions.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

EXPOSURE LIMIT VALUES

HAZARDOUS INGREDIENT	LTEL (8hr TWA) ppm	LTEL (8hr TWA) mg/m3	STEL (15 mins) ppm	STEL (15 mins) mg/m3	Notes
NAPHTHA (PETROLEUM), HYDRODESULFURIZED HEAVY		600			OEL
PROPANE	500	900			
BUTANE(CONT.<0.1%BUTADIENE)	600	1430	750	1780	WEL

OEL - Occupational Exposure Limits
 WEL - Workplace Exposure Limit
 SUP - Manufacturer's recommended Limit
 LTEL - Long-term Exposure Limit.
 TWA - Time weighted Average
 STEL - Short term Exposure Limit (15mins)
 sk - Risk of absorption through unbroken skin
 sen - Respiratory sensitiser
 rd - Figure quoted is for Respirable dust
 id - Figure quoted is for Inhalable dust
 Further guidance on WELs and OELs, and on occupational exposure to harmful materials (including mixed exposures) is given in HSE Guidance Note EH40.

EXPOSURE CONTROLS

Before commencing work, ensure that a COSHH Assessment has been carried out. All personal protective equipment, including

respiratory protective equipment, used to control exposure to hazardous substances must be selected to meet the requirements of local regulations.

RESPIRATORY PROTECTION: Avoid the inhalation of vapour, particulates and spray mist. Where reasonably practicable, this should be achieved by the use of local exhaust ventilation and good general ventilation. If this is not sufficient to maintain concentrations of particulates and solvent vapour below the occupational exposure limit, respiratory protection must be worn.

The selection of respiratory equipment should be in accordance with BS 4275. Recommendations for the selection, use and maintenance of Respiratory Equipment, and the current certificates of approval are issued annually by the Health and Safety Executive.

HAND PROTECTION: Wear suitable gloves for protection against materials in section 3.

When skin exposure may occur, advice should be sought from glove suppliers on appropriate types and usage times for this product. The instructions and information provided by the glove supplier on use, storage, maintenance and replacement must be followed.

EYE PROTECTION: Eye protection designed to protect against liquid splashes should be worn.

SKIN PROTECTION: Cotton or cotton/synthetic overalls or coveralls are normally suitable. Grossly contaminated clothing should be removed and the skin washed with soap and water or a proprietary skin cleaner.

ENVIRONMENTAL EXPOSURE CONTROLS: See section 12 for detailed information.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State :	Aerosol	
Flash Point :	< - 18	°C
Initial Boiling Point :	30	°C
Specific Gravity :	0.7	
Water Miscibility :	No Information	
pH :	No Information	
Viscosity :	< 30	(ISO 6mm Range)

Explosion limits: Lower - approx. 0.8% Upper - no information

10. STABILITY AND REACTIVITY

CONDITIONS TO AVOID: Extremes of temperature.

To prevent the creation of flammable concentrations of vapour in air, good natural ventilation, and if necessary, local exhaust ventilation, should be provided. The accumulation of dry overspray, contaminated rags, etc may result in spontaneous combustion. Good housekeeping standards plus the regular and safe removal of waste materials will minimise the risk.

MATERIALS TO AVOID: Keep away from oxidising agents, strongly alkaline and strongly acidic materials in order to avoid exothermic reactions.

HAZARDOUS DECOMPOSITION PRODUCTS: When exposed to high temperatures may produce hazardous decomposition products such as carbon monoxide and dioxide, smoke and oxides of nitrogen.

11. TOXICOLOGICAL INFORMATION

There is no data available on the product itself. The product has been assessed following the conventional method in the CHIP Regulations and is classified for toxicological hazards accordingly. This takes into account, where known, delayed and immediate effects and also chronic effects of components from short-term and long-term exposure by oral, inhalation and dermal routes of exposure and eye contact. See Sections 2 and 15 for details of the resulting hazard classification.

Over-exposures of vapour are irritating to eyes and respiratory system. Excessive concentrations may produce effects on the central nervous system including drowsiness. In extreme cases loss of consciousness may result. Long term exposure to vapour concentrations in excess of quoted OELs may result in adverse health effects. Splashes entering the eye will cause discomfort and possible damage. Prolonged contact with the skin may have a defatting effect which may lead to skin irritation and in some cases dermatitis.

Applicable to BLACK only:

In the case of pitches and tars there is a risk of the development of skin warts from prolonged contact. One type of wart is a cancer which if identified early can be treated and cured. Special care should be paid to personal hygiene.

12. ECOLOGICAL INFORMATION

There is no specific data available on the product itself.

The product should not be allowed to enter drains or watercourses or be deposited where it can affect ground or surface waters.

The Air Pollution Control requirements of regulations made under the Environmental Protection Act may apply to the use of this product.

Products classified as Marine Pollutants are indicated as such under Transport (section 14).

Products classified as Dangerous For the Environment are indicated as such in sections 2 and 15.

Any substances in the product that are classified as Dangerous for the Environment, present at concentrations above those requiring listing are given in section 3.

13. DISPOSAL CONSIDERATIONS

Wastes, including emptied containers, should be disposed of in accordance with national regulations.

CODES ACCORDING TO THE LIST OF WASTES REGULATIONS:

Product as supplied: Assigned as hazardous waste code 08 01 11* waste paint and varnish containing organic solvents or other dangerous substances.

Part-used containers, containing dried residues of the supplied product: Assigned as hazardous waste code 08 01 11* waste paint and varnish containing organic solvents or other dangerous substances

Used containers, rigorously scraped out and containing dried residues of the supplied product: Not Applicable.

"Rigorously scraped out" means removing the maximum amount of product from the container by physical or mechanical means (draining or scraping) to leave a residue or contamination that cannot be removed by such means.

These codes have been assigned based on the actual composition of the product both as supplied and as dried residues. If mixed with other wastes, the waste codes quoted may not be applicable.

14. TRANSPORT INFORMATION

Transport within user's premises:

Always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

Transport to be in accordance with ADR for road, IMDG for sea. The transport classifications provided in this section are not valid for transport by Air. Please call the number in section 1 of this safety data sheet to obtain more information on this products classification for Air transport.

ADR Classification Information

UN Number : 1950
 Proper Shipping Name : AEROSOLS
 Hazard Class : 2
 Sub-Hazard Class :
 Packing Group : .
 Technical Name (NOS only) :
 Ltd Qty Code : LQ2
 Packing Instructions : P204

IMDG Classification Information

UN Number : 1950
 Proper Shipping Name : AEROSOLS
 Hazard Class : 2
 Sub-Hazard Class :
 Packing Group :
 Technical Name (NOS only) :
 Ltd Qty Maximum : See SP277
 Packing Instructions : P003
 Marine Pollutant if indicated here: * MARINE POLLUTANT *
 Emergency Schedule No : F-D,S-U
 Flashpoint : < - 18

15. REGULATORY INFORMATION

This product has been assessed under the CHIP Regulations and is classified as follows:

For BLACK:

NAMED SUBSTANCES

Contains

PETROLEUM BITUMEN

INDICATION(S) OF DANGER

Extremely Flammable, Dangerous For The Environment, Harmful

SYMBOLS LETTER(S)

F+, N, Xn

WARNING LABEL PHRASES:

J37	SOLVENT-BASED PAINT.
R40	Limited evidence of a carcinogenic effect.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R66	Repeated exposure may cause skin dryness or cracking.
P96	Pressurised container: protect from sunlight and do not expose to temperature exceeding 50 degrees C. Do not pierce or burn, even after use.
P97	Do not spray on a naked flame or any incandescent material. Keep away from sources of ignition – No smoking. Keep out of the reach of children.
A6	Solvent abuse can kill instantly.
S9	Keep container in a well-ventilated place.
S51	Use only in well ventilated areas.
J103	Ensure maximum ventilation during application and drying.
S23	Do not breathe vapour/spray.
S38	In case of insufficient ventilation, wear suitable respiratory equipment.
S24/25	Avoid contact with skin and eyes.
J33	When applying it is advisable to wear eye protection.
S36/37	Wear suitable protective clothing and gloves.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
J34	After contact with skin, wash immediately with plenty of soap and water or a proprietary skin cleanser. Do not use solvent, thinners or white spirit.
S13	Keep away from food, drink and animal feedingstuffs.
S46	If swallowed, seek medical advice immediately and show this container or label.
J16	Do not empty into drains or watercourses. Some local authorities have special facilities for disposing of waste paint.
S61	Avoid release to the environment. Refer to special instructions/Safety data sheet.
J110	This includes waste hazard categories.
J47	For further advice contact ICI Paints AkzoNobel.

Label phrase according to the Volatile Organic Compounds in Paints, Varnishes and Vehicle Refinishing Products Regulations:

EU limit value for this product (cat B/e) : 840g/l

This product contains max. 699g/l VOC

For CLEAR:

NAMED SUBSTANCES

Contains

No substances are required to be named in this section

INDICATION(S) OF DANGER

Extremely Flammable, Dangerous For The Environment

SYMBOLS LETTER(S)

F+, N

WARNING LABEL PHRASES:

J37	SOLVENT-BASED PAINT.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R66	Repeated exposure may cause skin dryness or cracking.
P96	Pressurised container: protect from sunlight and do not expose to temperature exceeding 50 degrees C. Do not pierce or burn, even after use.
P97	Do not spray on a naked flame or any incandescent material. Keep away from sources of ignition – No smoking. Keep out of the reach of children.
A6	Solvent abuse can kill instantly.
S9	Keep container in a well-ventilated place.
S51	Use only in well ventilated areas.
J103	Ensure maximum ventilation during application and drying.
S23	Do not breathe vapour/spray.
S38	In case of insufficient ventilation, wear suitable respiratory equipment.
S24/25	Avoid contact with skin and eyes.
J33	When applying it is advisable to wear eye protection.
S36/37	Wear suitable protective clothing and gloves.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
J34	After contact with skin, wash immediately with plenty of soap and water or a proprietary skin cleanser. Do not use solvent, thinners or white spirit.
S46	If swallowed, seek medical advice immediately and show this container or label.
J16	Do not empty into drains or watercourses. Some local authorities have special facilities for disposing of waste paint.
S61	Avoid release to the environment. Refer to special instructions/Safety data sheet.
J110	This includes waste hazard categories.
J47	For further advice contact ICI Paints AkzoNobel.

Label phrase according to the Volatile Organic Compounds in Paints, Varnishes and Vehicle Refinishing Products Regulations:

EU limit value for this product (cat B/e) : 840g/l

This product contains max. 699g/l VOC

Where 'J' and/or 'P' phrases are denoted, these are ICI Paints or paint industry reference codes to additional phrases.

16. OTHER INFORMATION

Text for R Phrases shown in section 3 describing each ingredient:

R10	Flammable.
R12	Extremely flammable.
R36	Irritating to eyes.
R38	Irritating to skin.
R40	Limited evidence of a carcinogenic effect.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R65	Harmful: may cause lung damage if swallowed.
R66	Repeated exposure may cause skin dryness or cracking.

The information in this safety data sheet is required in pursuant to the CHIP Regulations.

Other Reference: The Control of Substances Hazardous to Health Regulations (COSHH). You should satisfy yourself that your COSHH Assessment is in accordance with the COSHH Regulations and Approved Code of Practice. ICI does not accept any responsibility for your COSHH Assessment.

The information on this sheet is not a specification: it does not guarantee specific properties. The information is intended to provide general guidance as to health and safety based upon our knowledge of the handling, storage and use of the product. It is not applicable to unusual or non-standard uses of the product nor where instructions and recommendations are not followed.

We will be pleased to answer any specific enquiries regarding the safe use, storage and handling of our product.
Contact: ICI PAINTS Technical Group, Wexham Road, Slough, Berks. SL2 5DS
Telephone: 0870 242 1100

ICI Paints in the UK is part of Imperial Chemical Industries plc and a member of the ICI Paints World Group. Registered in England No. 218019.
Registered office: 20 Manchester Square, London, W1U 3AN.

REVISION 04/2010: CHANGES TO SECTION 1,15 COMPARED WITH PREVIOUS VERSION DATED 02/2007 WHICH IS NOW SUPERSEDED.