



Save as PDF



35QT Elite Cooler



Interior dimensions:
40 x 30.5 x 29.2 cm (16" x 12" x 12")

*Ice retention - Initial test results are based on the Peli 65Qt Elite Cooler model. Testing was conducted using forced air circulation in a temperature controlled environmental chamber at 90 degrees F (32° C). The test specimens were loaded to capacity with commercial cubed ice. Performance will vary by model size and external user conditions, such as; (sun exposure, wind, ice type, frequency of opening, etc.).

- Dual Handle System (Moulded-in & Hinged Handles)
- Dual Handle System (Moulded-in & Hinged Handles)
- Press & Pull Latches (Wide for Gloved Use)
- Moulded-In Tie Downs
- Non-Skid & Non-Marking Raised Feet
- Moulded-In Lock Hasp, Stainless Steel Plate
- Sloped Drain & Tethered Threaded Plug (Garden Hose Attachable)
- Corrosion Resistant Stainless Steel Hardware
- Integrated Fish Scale on Lid
- Legendary Guarantee of Excellence
- Assembled in the USA with US and foreign components



White_132

35QT Elite Cooler SPECIFICATIONS

Exterior Dimensions (L x W x D)		Interior Dimensions (L x W x D)	
67.1 x 50.8 x 47.6 cm (26" x 20" x 19")		40 x 30.5 x 29.2 cm (16" x 12" x 12")	
Lid Depth	Bottom Depth	Total Depth	
0 cm (0")	0 cm (")	0 cm (")	
Lid Depth	Bottom Depth	Total Depth	
0 cm (")	0 cm (")	0 cm (")	
Weight w/Foam	Weight w/o Foam	Buoyancy Max.	
0 kg. (lbs)	0kg (lbs.)	0 kg (lbs.)	

Materials

Body	Latch	Lid O-Ring	Pins
	ABS		
Foam	Purge Body	Purge Vent	Purge O-Ring

Configuration

Cat. #	Description
35QT	35QT Elite Cooler

35QT Elite Cooler Accessories

No accessories are currently available for this product