

Electr. Digital Caliper • IP67

DIN 862

- professional standard caliper
- water and coolant proof acc. to DIN 40050 / IEC 60529
- with integrated Bluetooth® technology (max. 5m distance)

- mechanic parts stainless, hardened steel
- large LCD display with clear reading, digit height 13 mm
- measuring jaws finely ground and lapped
- On/Off-button, with fixing screw, with thumbroll
- mm/inch switchable, zero-setting at any position
- incl. 2x 3 V battery (type CR2032, art. no. 90112), with operation manual

Option

- data transfer via Bluetooth®, art. no.: 2023106, see page 272



ART No								
202420-2	150 / 6	0.01 / 0.0005	0.01	0.02	40	16.5	flat	on request
202421-2	200 / 8	0.01 / 0.0005	0.01	0.02	50	19.5	flat	on request
202422-2	300 / 12	0.01 / 0.0005	0.01	0.03	60	20.5	flat	on request

Electr. Digital Caliper • IP54

DIN 862

- standard caliper
- with glass rail for more accuracy
- spray water proof acc. to DIN 40050 / IEC 60529

- sturdy quality, stainless steel, hardened
- large LCD display with clear reading, 9 mm digit height
- jaws finely ground and lapped, with fixing screw
- On/Off button, with ABS/INC measuring system
- graduation in mm or inch, zero setting at any position
- incl. 1x 3 V battery (type CR2032, art. no. 90112), with operation manual



ART No								
202160-2	150 / 6	0.01 / 0.0005	0.01	0.02	40	16	flat	on request
202161-2	200 / 8	0.01 / 0.0005	0.01	0.03	50	19.5	flat	on request
202162-2	300 / 12	0.01 / 0.0005	0.01	0.03	60	20.5	flat	on request

Electr. Digital Caliper


DIN 862

- standard caliper
- with glass rail for more accuracy
- housing with metal cover and metal buttons
- with data output (mini USB)

- sturdy quality, stainless steel, hardened
- with or without thumbroll (included, for self installation)
- large LCD display with clear reading, 9 mm digit height
- jaws finely ground and lapped
- On/Off-button, with flat or round depth gauge
- mm/inch switchable, zero setting at any position
- incl. 1x 3 V battery (type CR2032, art. no.: 90112), with operation manual

Option

- data transfer via cable, art. no.: 209001, see page 272



ART No								
202040-3	150 / 6	0.01 / 0.0005	0.01	0.02	40	16.5	flat	on request
202041-3	200 / 8	0.01 / 0.0005	0.01	0.03	50	19.5	flat	on request
202042-3	300 / 12	0.01 / 0.0005	0.01	0.03	60	20.5	flat	on request
202043-3	150 / 6	0.01 / 0.0005	0.01	0.02	40	16.5	round	on request