



# FX0-ST1068002

Safe EFI-pro System

SAFETY SYSTEMS


**SICK**  
Sensor Intelligence.



### Ordering information

	Number of non-safe inputs	Number of non-safe outputs	Type	Part no.
I/O modules	6-8	6-8	FX0-STIO68002	1061778

Other models and accessories → [www.sick.com/Safe\\_EFI-pro\\_System](http://www.sick.com/Safe_EFI-pro_System)



### Detailed technical data

#### Features

<b>Module</b>	I/O module
<b>Configuration method</b>	Via software (Flexi Soft Designer) Safe EFI-pro System: Safety Designer

#### Interfaces

<b>Number of non-safe inputs</b>	6-8 <sup>1)</sup>
<b>Number of non-safe outputs</b>	6-8 <sup>1)</sup>
<b>Connection type</b>	Spring terminals

<sup>1)</sup> The FX0-STIO features 6 non-safe inputs and 6 non-safe outputs. In addition, 2 connections can be used both as non-safe inputs and non-safe outputs.

#### Electrical data

<b>Protection class</b>	III (EN 61140)
<b>Voltage supply</b>	Via FLEXBUS+
<b>Internal power consumption</b>	≤ 1.5 W <sup>1)</sup>
<b>Inputs</b>	
Input voltage HIGH	13 V DC ... 30 V DC
Input voltage LOW	-5 V DC ... 5 V DC
Input current HIGH	2.4 mA ... 3.8 mA
Input current LOW	-2.5 mA ... 2.1 mA
<b>Outputs</b>	
Voltage supply	Via A1, A2
Supply voltage	24 V DC (16.8 V DC ... 30 V DC)
Type of supply voltage	PELV or SELV <sup>2)</sup>
Type of output	PNP semiconductors, short-circuit protected

<sup>1)</sup> Via FLEXBUS+.

<sup>2)</sup> The current of the power supply that powers the module must be limited to a maximum of 4 A, either through the power supply itself or a fuse.

Output voltage HIGH	16 V DC ... 30 V DC
Output current	≤ 500 mA

<sup>1)</sup> Via FLEXBUS+.

<sup>2)</sup> The current of the power supply that powers the module must be limited to a maximum of 4 A, either through the power supply itself or a fuse.

## Mechanical data

<b>Dimensions (W x H x D)</b>	22.5 mm x 96.5 mm x 120.6 mm
<b>Weight</b>	139 g (± 5 %)

## Ambient data

<b>Enclosure rating</b>	IP20 (EN 60529)
<b>Ambient operating temperature</b>	-25 °C ... +55 °C
<b>Storage temperature</b>	-25 °C ... +70 °C
<b>Air humidity</b>	10 % ... 95 %, Non-condensing

## Classifications

<b>ECl@ss 5.0</b>	27243001
<b>ECl@ss 5.1.4</b>	27243101
<b>ECl@ss 6.0</b>	27243101
<b>ECl@ss 6.2</b>	27243101
<b>ECl@ss 7.0</b>	27243101
<b>ECl@ss 8.0</b>	27243101
<b>ECl@ss 8.1</b>	27243101
<b>ECl@ss 9.0</b>	27243101
<b>ECl@ss 10.0</b>	27243101
<b>ECl@ss 11.0</b>	27243101
<b>ETIM 5.0</b>	EC001449
<b>ETIM 6.0</b>	EC001449
<b>ETIM 7.0</b>	EC001449
<b>UNSPSC 16.0901</b>	32151705

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)