

## PRODUCT-DETAILS

# 22L001

## INSUL PIERCE SPLICE CU 26-17 AWG



### General Information

Extended Product Type	22L001
Product ID	7TAI029030R0018
EAN	5414363077114
Catalog Description	INSUL PIERCE SPLICE CU 26-17 AWG
Long Description	Insulation Piercing Magnet Wire Splice, Length .32 Inches, Width .16 Inches, Height .16 Inches, Wire Range #26 AWG - #17 AWG 808 Circular Mil Area - 5,162 Circular Mil Area, Copper Alloy, Tin Plated

### Ordering

EAN	5414363077114
UPC	786210892467

### Dimensions

Product Net Length	0, mm
--------------------	-------

### Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	2.8 in 71 mm
Package Level 1 Height	2.3 in

	58 mm
Package Level 1 Depth / Length	3.3 in 84 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	5.5 in 140 mm
Package Level 2 Height	3.3 in 84 mm
Package Level 2 Depth / Length	7.3 in 185 mm

## Additional Information

Application	For aluminum to copper, aluminum to aluminum or copper to copper magnet wire connections.
Brand / Label	Sta-Kon
Effective Date	19770803
Material	Copper
Number of Batteries	0
Product Name	ELECTRICAL TERMINAL, SPLICE
Product Type	Splice
Special Functions	Designed to penetrate magnet wire insulation during application, eliminating the need for stripping, brazing, welding or other methods of joining magnet wire.
Standards	UL E9809
Surface Finishing	Tin Plated

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	22L001
Instructions and Manuals	22L001

## Classifications

ETIM 6	EC001059 - Crimp splices for copper conductor
ETIM 7	EC001059 - Crimp splices for copper conductor
UNSPSC	39121449
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4669 >> Wire or cable compression splice

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

