



## Main

Range compatibility	Lexium 23 Plus
Product or component type	Servo motor
Device short name	BCH



## Complementary

Maximum mechanical speed	5000 rpm
[Us] rated supply voltage	220 V
Network number of phases	Single phase
Continuous stall current	2.6 A
Continuous power	0.4 kW
Shaft end	Keyed
Second shaft	Without second shaft end
Shaft diameter	14 mm
Shaft length	24 mm
Key width	5 mm
Feedback type	20 bits incremental encoder
Holding brake	Without
Mounting support	Asian standard flange
Motor flange size	60 mm
Torque constant	0.49 N.m/A
Back emf constant	17.4 V/krpm at 20 °C
Rotor inertia	0.277 kg.cm <sup>2</sup>
Stator resistance	3.1 Ohm at 20 °C
Stator inductance	13.42 mH at 20 °C
Stator electrical time constant	4.3 ms at 20 °C
Maximum radial force Fr	196 N
Maximum axial force Fa	68 N
Brake pull-in power	6.5 W
Type of cooling	Natural convection
Length	130.7 mm
Number of motor stacks	2
Centring collar diameter	50 mm
Centring collar depth	3 mm
Number of mounting holes	4
Mounting holes diameter	5.5 mm
Circle diameter of the mounting holes	70 mm
Distance shaft shoulder-flange	24 mm
Product weight	1.6 kg


## Environment

IP degree of protection	IP40
Ambient air temperature for operation	0.0 °C...40.0 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
Product environmental profile	Available  <a href="#">Download Product Environmental</a>  <a href="#">Product Environmental</a>
Product end of life instructions	Need no specific recycling operations

## Dimensions



(1) Shaft end, keyed slot (optional)

Dimensions in mm

c (without holding brake)	c (with holding brake)
130.7	166.8

Dimensions in in.


c (without holding brake)	c (with holding brake)
5.14	6.57

---

Torque/Speed Curves with 220 V Single Phase Supply Voltage

---

Servo Motor with LXM23•U04M3X Servo Drive



M : Torque in Nm

n : Speed in rpm

1 : Peak torque

2 : Continuous torque