


Geberit Mapress ball valve, NPW, with actuator lever



Example image

APPLICATION PURPOSES

- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For compressed air (oil purity class 0–3)
- For installations with Geberit Mapress Carbon Steel
- For installations with Geberit Mapress Copper

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Operating temperature -20 – +120 °C
Product material Brass CW617N

INFO

- The ball valves are marked with PN 10 on the body in accordance with DVGW and EN 13828
- The ball valves are approved for up to PN 16
- Ausschliesslich mit Geberit Mapress C-Stahl oder Geberit Mapress Kupfer Systemrohren verwenden

CHARACTERISTICS

- Ball made of brass, chrome-plated

Art. no.	DNV	DN	d, ø mm	L cm	L1 cm	L2 cm	Z cm	Z1 cm	PN bar
94922	15	12	15	7.7	4.4	8.5	1.7	2.4	16
94923	15	15	18	8	4.4	8.5	1.7	2.4	16
94924	20	20	22	8.9	5.2	10.6	2.1	2.9	16

<i>Art. no.</i>	<i>DNV</i>	<i>DN</i>	<i>d, ø mm</i>	<i>L cm</i>	<i>L1 cm</i>	<i>L2 cm</i>	<i>Z cm</i>	<i>Z1 cm</i>	<i>PN bar</i>
94925	25	25	28	9.6	5.6	10.6	2.4	3.1	16
94926	32	32	35	10.9	6.1	10.6	2.7	3.4	16
94927	40	40	42	14.1	7.9	15.5	3.6	4.5	16
94928	50	50	54	15.7	9.4	17.5	3.9	4.8	16