



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	User manual Wall-mounting template
--------------------	---------------------------------------

Physical

Cable length	1.83 m
Colour	Charcoal
Depth	28.5 cm
Height	8.6 cm
Net weight	5.4 kg
Width	23 cm

Input

Network frequency	50/60 Hz
Plug standard	CEI 23-16 Italian
Input voltage limits	180...266 V
Maximum input current	10 A
Input voltage	230 V

Output

Rated power in W	240 W
Maximum configurable power in W	240 W
Output frequency	47...63 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
UPS type	Standby
Wave type	Stepped approximation to a sinewave

Nb of power socket outlets	4 Schuko CEE 7 4 Schuko CEE 7 surge
Output voltage	230 V

Conformance

Product certifications	CE
Equipment protection policy	Lifetime : 100000 euros

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...50000 ft
Ambient air temperature for storage	0...40 °C
Storage altitude	0.00...15240.00 m
Acoustic level	45 dBA

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	16 h
Number of battery replacement quantity	1
Liquid value	0

Communications & Management

Control panel	LED Status display with on line : on battery
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rate	310 J
Noise suppression	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449
Data line protection	RJ11 analog phone line for phone/fax/modem/DSL RJ45 network line - 10/100 base-T Ethernet

Packing Units

Package 1 Weight	5.6 kg
Package 1 Height	13.2 cm
Package 1 width	30 cm
Package 1 Length	36.6 cm
SCC14	10731304233388
Number of Units in Package 2	2
Package 2 Weight	12.17 kg
Package 2 Length	381.00 mm
Number of Units in Package 3	48

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration

Mercury free	Yes
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Contractual warranty	
Warranty	3 years repair or replace