
**NUTR35** **Galet de roulement**

Yoke type track rollers NUTR...-A, double row cylindrical roller bearings with particularly thick-walled outer ring, full complement cylindrical roller set and an inner ring, the outer ring is guided axially by the rolling elements, labyrinth seals on both sides

Information technique**Votre alternative produit actuelle**

joint	2LB	Labyrinth seals on both sides
profile bague extérieure	IOP	Optimized INA-profile
dispositif de lubrification	IR	Via inner ring

dimensions principale & données de performance

d	35 mm	Alésage
D	72 mm	Diamètre extérieur
B	29 mm	Largeur, bague intérieure
C _{r w}	45.500 N	Charge dyn. de base, radiale
C _{0r w}	65.000 N	Charge stat. de base, radiale
C _{ur w}	8.900 N	Limite à la fatigue, radiale
n _{D G}	2.100 1/min	Vitesse pour une lubrification à la graisse
F _{0r per}	62.000 N	Charge radiale statique admissible
F _{r per}	31.500 N	Charge radial dynamique admissible sur bague extérieure
≈m	0,629 kg	Poids

Dimensions

C	28 mm	Largeur, bague extérieure
d ₂	44 mm	Diamètre d'arrêt rondelle de butée
r _{min}	1,1 mm	Dimension minimum de chanfrein
r _{1 min}	0,6 mm	Dimension minimum de chanfrein