

G-INSEC-M25-S68N-NCRS-S - Cable gland



1411190

<https://www.phoenixcontact.com/gb/products/1411190>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: Brass, nickel-plated, application: EMC, external cable diameter 11 mm ... 16 mm, shielding: yes, connecting thread: M25 x 1.5, color: silver-colored, with O-ring

Commercial data

Item number	1411190
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AF7DBX
Product key	AF7DBX
Catalog page	Page 690 (C-2-2019)
GTIN	4046356923217
Weight per piece (including packing)	58.572 g
Weight per piece (excluding packing)	56 g
Customs tariff number	74198090
Country of origin	DE

G-INSEC-M25-S68N-NCRS-S - Cable gland



1411190

<https://www.phoenixcontact.com/gb/products/1411190>

Technical data

Mounting

Assembly note	<p>Method 1</p> <p>Cut the outer sheath, but do not remove it. Feed the cable through the screw connection and then remove the outer sheath. Now pull the cable back until the connection is established between the cable shield and the contact spring.</p> <p>Method 2</p> <p>Push the braided shield back around 15 ... 20 mm over the outer sheath. Insert the cables into the screw connection until the connection is established between the cable shield and the contact spring.</p>
---------------	---


Product properties

Product type	Cable screw gland
Application	EMC
No. of conductors	1
Manufacturer	Jacob
Manufacturer Designation	50.625 M/EMVD
Shielded	yes
Execution of the strain relief	A

Characteristics

Category of shock impact	6
Design, Strain relief	A

Dimensions

Dimensional drawing	
Length	36 mm
Length of the connecting thread	7 mm
Hole diameter	25.1 mm ... 25.2 mm
Wrench size, union nut	27 mm
Wrench size, support	27 mm
Hexagon angular dimension	30 mm
Thread type connection side	M25 x 1.5
Thread pitch	1.5 mm

Connection data

Tightening torque	6.7 Nm (Union nut: EN 62444)
	6.7 Nm (Support: EN 62444)

G-INSEC-M25-S68N-NCRS-S - Cable gland



1411190

<https://www.phoenixcontact.com/gb/products/1411190>

Material specifications

Color	brass color
Material Compression ring	PA 6
Seal material O-ring	Perbunan
Seal material Cable seal	CR/NBR
Material for screw connection	Brass, nickel-plated

Cable/line

External cable diameter Cable 1	11 mm ... 16 mm
Halogen-free	no

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68 (5 bar, 30 minutes)
Ambient temperature (operation)	-40 °C ... 100 °C (static)


G-INSEC-M25-S68N-NCRS-S - Cable gland

1411190

<https://www.phoenixcontact.com/gb/products/1411190>


Drawings

Dimensional drawing



Dimensional drawing

Functional drawing



See assembly instruction

G-INSEC-M25-S68N-NCRS-S - Cable gland




1411190


<https://www.phoenixcontact.com/gb/products/1411190>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1411190>




cUL Recognized
Approval ID: QCRV8.E140310



UL Recognized
Approval ID: QCRV2.E140310



UL Listed
Approval ID: QCRV.E140310



cUL Listed
Approval ID: QCRV7.E140310

G-INSEC-M25-S68N-NCRS-S - Cable gland



1411190

<https://www.phoenixcontact.com/gb/products/1411190>

Classifications

ECLASS

ECLASS-13.0	27140801
-------------	----------

ETIM

ETIM 9.0	EC000441
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

G-INSEC-M25-S68N-NCRS-S - Cable gland



1411190

<https://www.phoenixcontact.com/gb/products/1411190>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	aea90f92-c228-4617-877a-cd492e4d0291

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk