

VDE 4508-02

VDE Torque wrench


5-50 Nm

Code
3125335 ETIM
EC002132

EAN
4002805937303 UNSPSC
27-11-17-15

Country of origin
Germany eCI@ss
21-04-01-01

Customs tariff number
82041100



IEC 60900/IEC 60900-1 1000V

Article description

- Controlled screw tightening in the most widely used range
- Release system triggers a tactile and audible signal
- Scale with Nm division
- Classified according to DIN EN ISO 6789-2:2017 Type II Class A, incl. traceable test certificate, calibrated to a maximum permissible deviation of +/- 3 % and thus more precise than the +/- 4 % required by the standard
- Recalibration without destroying the insulation
- Fine toothed ratchet with square drive as per DIN 3120, ISO 1174
- Safety button to protect against accidental release of the insert
- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900

Article information

Contents [Qty of pieces]	1	Torque range [min./max.] [lbf·ft]	-
Net weight [kg]	0,714 kg	Trigger mechanism	Short path triggering
Total length [mm]	319 mm	Precision +/-	+/- 4 %
Total width [mm]	48 mm	Direction of tightening	Right
Total height [mm]	75 mm	Fixed setting	no
Drive connector square (male)	3/8"	Test certificate	DIN EN ISO 6789-2:2017
Drive connector square (male)	10 mm	Graduation	1
Return angle	5°	Head height 1 [mm]	62 mm
Number of teeth	72	Width of head 1 [mm]	50,0 mm
Drive type/drive	Reversible ratchet	Calibration length	229 mm
Torque [min.] [N·m]	5 Nm	vernier Nm	0,1 Nm
Torque [max.] [N·m]	25 Nm	Distance housing - square drive	24 mm
Torque range [min./max.] [N·m]	5 Nm - 25 Nm	Storage/Content	Plastic box