

Valve connectors - SACC-V-4CON-PG9/A - 1527883


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Valve connectors, 4-position, Valve connector A, Screw connection, cable gland Pg9, external cable diameter 6 mm ... 8 mm



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 017918 980955 |
| GTIN | 4017918980955 |
| Weight per Piece (excluding packing) | 25.300 g |
| Custom tariff number | 85366990 |
| Country of origin | Hungary |

Technical data

Dimensions

| | |
|-------------------|---------------|
| External diameter | 6 mm ... 8 mm |
|-------------------|---------------|

Ambient conditions

| | |
|---------------------------------|-------------------------------|
| Ambient temperature (operation) | -30 °C ... 100 °C (connector) |
| Degree of protection | IP65 |

General

| | |
|------------------------------|----------|
| Rated current at 40°C | 10 A |
| Rated voltage | 250 V AC |
| | 250 V DC |
| Number of positions | 4 |
| Insulation resistance | ≥ 100 MΩ |
| Status display | No |
| Protective circuit/component | unwired |
| Overvoltage category | II |
| Degree of pollution | 3 |

Valve connectors - SACC-V-4CON-PG9/A - 1527883

Technical data

General

| | |
|-----------------------------|--|
| Connection method | Screw connection |
| Conductor cross section | 0.34 mm ² ... 1.5 mm ² |
| Conductor cross section AWG | 22 ... 16 |
| Insertion/withdrawal cycles | 50 (Valve connector) |

Material

| | |
|--|------------------------|
| Flammability rating according to UL 94 | HB |
| Valve plug contact material | CuSn |
| Valve plug contact surface material | Ni |
| Valve plug contact insert material | PA6 |
| Material housing valve plug | PA6 |
| Sealing material | NBR (Flat gasket) |
| | TPE (Screw connection) |

Standards and Regulations


| | |
|--|----|
| Connection in acc. with standard | UL |
| Flammability rating according to UL 94 | HB |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 50 |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Drawings

Dimensional drawing



Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27140815 |
| eCl@ss 4.1 | 27140815 |
| eCl@ss 5.0 | 27143423 |
| eCl@ss 5.1 | 27143400 |
| eCl@ss 6.0 | 27279200 |

Valve connectors - SACC-V-4CON-PG9/A - 1527883

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 7.0 | 27440104 |
| eCl@ss 8.0 | 27440104 |
| eCl@ss 9.0 | 27440105 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001121 |
| ETIM 3.0 | EC002062 |
| ETIM 4.0 | EC002062 |
| ETIM 5.0 | EC002062 |
| ETIM 6.0 | EC002925 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 31251501 |
| UNSPSC 7.0901 | 31251501 |
| UNSPSC 11 | 31251501 |
| UNSPSC 12.01 | 31251501 |
| UNSPSC 13.2 | 32151909 |

Approvals


Approvals

Approvals

UL Recognized / EAC

Ex Approvals

Approval details

| | | | |
|--------------------|---|---|---------------|
| UL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | File E 118976 |
| Nominal voltage UN | 250 V | | |
| Nominal current IN | 10 A | | |

| | | |
|-----|---|---------------|
| EAC |  | EAC-Zulassung |
|-----|---|---------------|

