

2-Post 6U Wall Mounted Rack, Adjustable Depth up to 16in (40cm), Bracket for 19-inch Server/Data/Networking Equipment, Open Frame, Max 88lb (40kg)

Product ID: WALLMOUNT6-HAF



This 2-post 6U adjustable wall mount bracket provides a convenient solution for mounting 19-inch rack-mountable shallow servers, patch panels, NAS devices, UPS, data, and networking equipment. The adjustable depth enables customization to accommodate various equipment sizes.

This wall-mounted rack features fold-out sides for quick setup, ships fully assembled flat-packed, and includes all the necessary hardware: wood stud screws, M5 cage nuts, and M5 screws and speed up deployment. Four keyhole wall mounting holes provide a straightforward way to securely mount or unmount the rack. The mounting holes are spaced 16" (40.6cm) to match existing wall-stud framework.

The 2-post open rack features an adjustable depth range from 9.6 to 15.6in (24.5 to 39.7cm) to accommodate larger rack-mountable devices. The additional depth can also be used for equipment that may require additional clearance at the back for cable management.

Wall-mount rack bracket is made from 14-gauge (2mm) SPCC steel that can support up to 88lb (40kg) of equipment, providing a stable and sturdy mounting point. The powder-coated finish ensures long-lasting durability, protecting the rack from wear and tear.

Certifications, Reports and Compatibility

Applications

Features

- 6U WALL MOUNT ADJUSTABLE RACK: 2-Post 6U wallmount rack supports 19-inch shallow server racks, shelves,

patch panels, UPS, data, and networking equipment; Adjustable mounting depth up to 15.6in (39.7cm) deep; EIA-310-compliant

- **READY TO USE:** Wall-mounted rack features fold-out sides for quick setup, ships fully assembled flat-packed, and includes wood stud screws, M5 cage nuts, and M5 screws; Four keyhole mounting holes ensure easy installation and removal
- **ADJUSTABLE DEPTH:** Customize the mounting depth from 9.6 to 15.6in (24.5 to 39.7cm) to accommodate different sized equipment; The side panels feature handles and preset adjustment holes for easy depth customization
- **WEIGHT CAPACITY AND MOUNTING:** This wall bracket can hold up to 88lb (40kg), providing a reliable solution for equipment mounting; Wall mounting holes are spaced 16" (40.6cm) apart enabling secure anchoring to existing construction framework
- **DURABLE STEEL CONSTRUCTION:** Built from 14-gauge (2mm) solid steel with a powder-coated finish, this open-frame rack delivers exceptional strength and durability for long-term mounting; Wall mount bracket is backed for life and 24/5 technical assistance

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	6U
Special Features	Ships Fully Assembled Wall-Mountable
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	88.2 lb [40 kg]
-----------------	-----------------

Physical Characteristics

Color	Black
Construction Material	Steel

Product Measurements

Product Length	20.1 in [510 mm]
----------------	------------------

Product Width	11.8 in [300 mm]
Product Height	1.3 in [33 mm]
Weight of Product	232.0 oz [6572 g]
Maximum Mounting Depth	15.7 in [397.7 mm]
Minimum Mounting Depth	9.7 in [245.3 mm]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	22.2 in [56.5 cm]
Package Width	14.8 in [37.5 cm]
Package Height	3.9 in [10.0 cm]
Shipping (Package) Weight	16.1 lb [7.3 kg]

What's in the Box

Included in Package	1 - 6U Wall Mount Rack
	12 - M5x15 Screws
	12 - M5 Cage Nuts
	4 - M8x50 Screws
	4 - M6x12 Screws
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***