

product type designation

product description

MM991-2P (SC RJ)

XR-300 media module

SCALANCE X accessory; Media module MM991-2P; 2x 100 Mbit/s; SC RJ POF/PCF ports; optical; POF up to max. 50 m, PCF up to max. 100 m.



interfaces

number of electrical/optical connections / for network components or terminal equipment / maximum	2
number of optical interfaces / for network components or terminal equipment / maximum	2
number of 100 Mbit/s SC ports / for multimode / integrated	0
number of 100 Mbit/s SC-RJ-ports	2
design of the optical interface / for network components or terminal equipment	SC RJ
wavelength / of the optical interface	650 nm; POF/PCF
connectable optical power relative to 1 mW	
• of the transmitter output / minimum	-8 dB
• of the transmitter output / maximum	-2 dB
• of the receiver input / maximum	1 dB
optical sensitivity relating to 1 mW / of the receiver input / minimum	23 dB
attenuation factor / of the FOC transmission link / minimum necessary	0 dB
range / at the optical interface / depending on the optical fiber used	0.001 ... 0.1 km

ambient conditions

ambient temperature	
• during operation	-25 ... +40 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20

design, dimensions and weights

design	Media module
width	60 mm
height	22 mm
depth	100 mm
net weight	0.08 kg
fastening method	latched
• installation in media module slot	Yes

standards, specifications, approvals

standard	
• for FM	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4

<ul style="list-style-type: none"> • for hazardous zone • for safety / from CSA and UL • for hazardous zone / from CSA and UL • for emitted interference • for interference immunity 	<p>EN 60079-0: 2006, EN60079-15: 2005, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X</p> <p>UL 60950-1, CSA C22.2 No. 60950-1</p> <p>UL 1604 and UL 2279-15 (Hazardous Location), CSA C22.2 No. 213-M1987, Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4</p> <p>EN 61000-6-4:2007 (Class A)</p> <p>EN 61000-6-2:2005</p>
<p>certificate of suitability</p> <ul style="list-style-type: none"> • CE marking • C-Tick • KC approval • CCC / for hazardous zone according to GB standard • CCC / for hazardous zone according to GB standard / as marking 	<p>EN 61000-6-2:2005, EN 61000-6-4:2007</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes; GB3836.1, GB3836.8</p> <p>Ex nA IIC T4 Gc</p>
<p>Marine classification association</p> <ul style="list-style-type: none"> • French marine classification society (BV) 	<p>Yes</p>
<p>MTBF</p>	<p>230 a</p>
<p>further information / internet links</p>	
<p>internet link</p> <ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support 	<p>http://www.siemens.com/tia-selection-tool</p> <p>http://www.siemens.com/simatic-net</p> <p>https://mall.industry.siemens.com</p> <p>http://www.siemens.com/industry/infocenter</p> <p>http://automation.siemens.com/bilddb</p> <p>http://www.siemens.com/cax</p> <p>https://support.industry.siemens.com</p>

last modified:

11/9/2023 