



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		AS1	REVISED PER ECO-11-004587	11MAR11	RK	HMR



$\triangle 7$	$\triangle 8$	3	46.08 [1.814]	25.91 [1.020]	6-66460-6
$\triangle 7$	$\triangle 8$	1	35.97 [1.416]	15.80 [.622]	6-66460-5
$\triangle 7$	$\triangle 4$	3	46.08 [1.814]	25.91 [1.020]	6-66460-4
$\triangle 7$	$\triangle 4$	2	41.28 [1.625]	21.11 [.831]	6-66460-3
$\triangle 7$	$\triangle 4$	1	35.97 [1.416]	15.80 [.622]	6-66460-2
$\triangle 2$	$\triangle 2$	SPECIAL	33.40 [1.315]	13.23 [.521]	6-66460-1
$\triangle 2$	$\triangle 3$	SPECIAL	65.61 [2.583]	45.44 [1.789]	5-66460-0
$\triangle 2$	$\triangle 3$	SPECIAL	57.73 [2.273]	37.57 [1.479]	4-66460-9
$\triangle 2$	$\triangle 3$	SPECIAL	49.86 [1.963]	29.69 [1.169]	4-66460-8
$\triangle 2$	$\triangle 3$	SPECIAL	68.60 [2.701]	48.44 [1.907]	3-66460-0
$\triangle 2$	$\triangle 3$	SPECIAL	59.71 [2.351]	39.55 [1.557]	2-66460-9
$\triangle 2$	$\triangle 3$	SPECIAL	50.82 [2.001]	30.66 [1.207]	2-66460-8
$\triangle 2$	$\triangle 4$	1	34.80 [1.370]	14.63 [.576]	2-66460-1
$\triangle 2$	$\triangle 4$	-	34.77 [1.369]	14.63 [.576]	2-66460-0
$\triangle 2$	$\triangle 4$	SPECIAL	52.78 [2.078]	32.61 [1.284]	1-66460-9
$\triangle 2$	$\triangle 5$	2	41.28 [1.625]	21.11 [.831]	1-66460-8
$\triangle 2$	$\triangle 4$	2	41.28 [1.625]	21.11 [.831]	1-66460-1
$\triangle 2$	$\triangle 4$	SPECIAL	33.40 [1.315]	13.23 [.521]	1-66460-0
$\triangle 2$	$\triangle 4$	3	46.08 [1.814]	25.91 [1.020]	66460-9
$\triangle 2$	$\triangle 4$	2	41.28 [1.625]	21.11 [.831]	66460-8
$\triangle 2$	$\triangle 4$	1	35.97 [1.416]	15.80 [.622]	66460-7
$\triangle 2$	$\triangle 3$	3	46.08 [1.814]	25.91 [1.020]	66460-6
$\triangle 2$	$\triangle 3$	2	41.28 [1.625]	21.11 [.831]	66460-5
$\triangle 2$	$\triangle 3$	1	35.97 [1.416]	15.80 [.622]	66460-4
$\triangle 2$	$\triangle 2$	3	46.08 [1.814]	25.91 [1.020]	66460-3
$\triangle 2$	$\triangle 2$	2	41.28 [1.625]	21.11 [.831]	66460-2
$\triangle 2$	$\triangle 2$	1	35.97 [1.416]	15.80 [.622]	66460-1
FINISH	BODY FINISH	NO OF TERM	B	A	PART NUMBER

- $\triangle 1$ BRASS PER ASTM B-36.
- $\triangle 2$ $2.54 \mu\text{m}$ [.000100] MIN TIN-LEAD OVER $1.27 \mu\text{m}$ [.000050] MIN NICKEL.
- $\triangle 3$ $0.76 \mu\text{m}$ [.000030] MIN PRECIOUS METAL PLATING CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS), OVER $1.27 \mu\text{m}$ [.000050] MIN NICKEL.
- $\triangle 4$ $0.76 \mu\text{m}$ [.000030] MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF 5.08 [.200] MIN OVER $1.27 \mu\text{m}$ [.000050] MIN NICKEL PLATE. GOLD FLASH ALL OVER. CONFORMS TO THE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01A (CONTROLLED ENVIRONMENT APPLICATIONS).
- $\triangle 5$ SELECTIVELY PLATED $0.51 \mu\text{m}$ [.000020] MIN GOLD, FOR A DISTANCE OF 5.08 [.200] FROM MATING END, GOLD FLASH ON REMAINDER, ALL OVER $0.76 \mu\text{m}$ [.000030] MIN NICKEL.
- $\triangle 6$ POST WILL ACCEPT (SEE TABLE) TERMINATIONS.
- $\triangle 7$ POST PLATING .000100 MIN TIN OVER .000050 MIN NICKEL.
- $\triangle 8$.0001000 TIN OVER .000050 NICKEL.

SUPERSEDED BY 66460-8

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C.REIFSNYDER
06 JUN 96

CHK
R.STONE
27 JUN 96

APVD
G.A.STEINHAUER
23 JUL 96

TE Connectivity

PIN CONTACT, CRIMPED,
.062, .025 X .025 POSST,
M SERIES

SIZE
A2

CAGE CODE
00779

DRAWING NO
66460

RESTRICTED TO
-

MATERIAL
SEE CALLOUTS

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC $\pm$ -
1 PLC $\pm$ -
2 PLC $\pm$ 0.25 [.010]
3 PLC $\pm$ -
4 PLC $\pm$ -
ANGLES $\pm$ -
FINISH
SEE CALLOUTS

WEIGHT
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 of 2

REV
AS1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, —

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC
FT

DIST
0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

7

4

SPECIAL

33.40
[1.315]

13.23
[.521]

6—66460—8

7

8

2

41.28
[1.625]

21.11
[.831]

6—66460—7

POST
FINISH

BODY
FINISH

NO. OF
TERM

B

A

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
SEE CALLOUTS

0 PLC ± —
1 PLC ± —
2 PLC ± 0.25 [.010]
3 PLC ± —
4 PLC ± —
ANGLES ± —

FINISH
SEE CALLOUTS

DWN
C.REIFSNYDER
06 JUN 96

CHK
R.STONE
27 JUN 96

APVD
G.A.STEINHAUER
23 JUL 96

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

TE Connectivity

NAME
PIN CONTACT, CRIMPED,
.062, .025 X .025 POSST,
M SERIES

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=66460

RESTRICTED TO
—

SCALE
4:1

SHEET
2 OF 2

REV
AS1

1471—9 (3/11)

66460

66460