



Specification  
CM95/CM100  
True RMS Flexible Clamp Meter



**ELECTRICAL**

All specified accuracies are at 23°C ± 5°C, <80% RH for 1 year.

**Temperature coefficient:** add 0.1 x (specified accuracy) per °C (0°C to 18°C, 28°C to 40°C)

Accuracies below are expressed as ± (percentage of reading + digits)

**AC Current**

CM95		
Range	Resolution	Accuracy (45Hz to 500Hz)
4A	0.001A	3.0% + 5 Note 1
40A	0.01A	
400A	0.1A	

CM100		
Range	Resolution	Accuracy (45Hz to 500Hz)
30A	0.01A	3.0% + 5 Note 1
300A	0.1A	
3000A	1A	



Specification  
CM95/CM100  
True RMS Flexible Clamp Meter

Dimensions: Meter: 120mm (L) x 70mm (W) x 26mm (D)  
Cable length (probe to meter): 1.8m  
Flexible sensor length: 254mm (CM95)  
458mm (CM100)  
Flexible sensor diameter: 5.5mm nominal (CM95)  
8.5mm nominal (CM100)  
Maximum conductor diameter: 85mm (CM95)  
160mm (CM100)  
Weight (including batteries): 196g approx. (CM95)  
286g approx. (CM100)  
Includes: 2 x 1.5V AAA batteries, instructions

**ENVIRONMENTAL**

Temperature & Humidity:  
(Operating): 0°C to 50°C <80% R.H., non-condensing  
(Storage): -10°C to 60°C <70% R.H., batteries removed  
Altitude: up to 2000m  
Pollution degree: 2

**SAFETY**

Conforms to: BS EN 61010-1, BS EN 61010-2-032, CAT IV 600V, CAT III 1000 V Class II, double insulation

**EMC**

Conforms to BS EN 61326-1



Specification  
CM95/CM100  
True RMS Flexible Clamp Meter

AC conversion: True rms

True rms AC current accuracy is specified from 2% of range to 100% of range. With an input of less than 2% of range the unit may indicate zero or indicate randomly.

Crest factor: ≤ 1.6 at full scale  
≤ 3.2 at half scale

Note 1: Measurement accuracy assumes a centrally positioned conductor, no external electrical or magnetic field and within operating temperature range. See figure 3 and the position sensitivity error table below for additional errors where the conductor is not centrally positioned.

Distance of conductor from loop centre	Position Sensitivity Error	
	Additional Error (% of reading)	
	CM95	CM100
1" (2.54cm)	1.0	1.0
1.6" (4.06cm)	2.0	1.0
2" (5.1cm)	---	2.0
3" (7.6cm)	---	3.0

**GENERAL**

Display: Liquid crystal display with maximum reading 4200 (CM95), 3150 (CM100)

Sample rate: 2 times/sec

Overrange: " — OL — " is displayed

Power: 2 x 1.5V, AAA alkaline batteries (IEC LR03, NEDA 24A)

Battery life: 120 hours typical with alkaline

Low battery indication: symbol is displayed

Auto power off: After 15 minutes

**Check out what else you can get from Martindale:**

- 17th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Safe Isolation kits
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited  
Metrohm House, Imperial Park, Imperial Way,  
Watford, Hertfordshire, WD24 4PP, UK  
Tel: +44 (0)1923 441717 Fax: +44 (0)1923 446900  
E-mail: sales@martindale-electric.co.uk  
Website: www.martindale-electric.co.uk



© 2016 Martindale Electric Company Ltd.  
Registered in England No. 3387451. Rev2 LITCM95/CM100