



Connectors > Connector Accessories > Connector Caps & Covers > Bus Connector: Strain Relief, ATA



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Black**

Primary Product Material: **Thermoplastic**

Number of Positions: **30**

[All Bus Connector: Strain Relief, ATA \(13\)](#)

Features

Product Type Features

Connector Cover Type	Strain Relief Cover
----------------------	---------------------

Configuration Features

Number of Positions	30
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	Thermoplastic

Dimensions

Product Width	6.1 mm[.24 in]
Product Length	42.93 mm[1.69 in]
Product Height	14.76 mm[.581 in]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	CSA LR7189, UL E28476

Packaging Features



Packaging Method	Bag & Box
Packaging Quantity	1

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1-1761606-0
IDC LOW PRO HDR 30P VERT LA



TE Part # 1658622-7
30 NOVO MIL/CTR 30DP, LEAD FREE



TE Part # 2-111504-0
030 UNIV I/O 30DP NO EARS LTCH



TE Part # 1658620-7
30 NOVO MIL 15DP, LEAD FREE




TE Part # 1658621-7
30 NOVO MIL/CTR 15DP,LEAD FREE



TE Part # 3-1761712-0
IDC LOW PRO HDR 30P RA LAT



TE Part # 1658624-7
30 NOVO DUAL 30DP, LEAD FREE



TE Part # 3-1761603-0
IDC LOW PRO HDR 30P VERT BLUE



TE Part # 2-111446-1
030 UNIV I/O 30DP NO EARS




TE Part # 1658623-7
30 NOVO MIL 30DP, LEAD FREE



TE Part # CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS

Customers Also Bought



TE Part #1609140-1
PA100=F6800




TE Part #5569256-1
STK MJ ASSY,8POS,2X3,SHLD,CAT5



TE Part #350833-1
04P UMNL HDR ASSY PC 94VO



TE Part #2-1625984-5
HSA50 1R2 5%



TE Part #644968-4
08P MTA156 HDR ASSY OMIT#5,7




TE Part #1658623-7
30 NOVO MIL 30DP, LEAD FREE




TE Part #640453-5
05P MTA100 HDR ASSY SQ R/A



TE Part #2-2232875-1
GIC6.0MM CONNECTOR PLUG HOUSING 2POS



TE Part #796690-8
TERMI-BLOK PCB MOUNT 8P



TE Part #768341-1
CONNECTOR SPECIFIC KIT STD

Documents



Product Drawings

030 STRAIN RELIEF A-L RCPT

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-499252-2_AL.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-499252-2_AL.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-499252-2_AL.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Ribbon Cable Interconnect Solutions

English

Product Specifications

Application Specification

English