




MATE-N-LOK | Universal MATE-N-LOK

TE Internal #: 926298-3

4 Position, Plug, Housing, Crimp, Wire-to-Wire, UL 94V-0, 6.35 mm [.25 in] Centerline, 1 Row, 600 VAC, Wire & Cable, Universal MATE-N-LOK

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**

Connector & Housing Type: **Plug**

Termination Method to Wire & Cable: **Crimp**

Connector System: **Wire-to-Wire**

Contact Retention Within Housing: **Without**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1
Number of Power Positions	0
Number of Signal Positions	0

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------



Contact Features

Multiple Contact Types	Without
Contact Layout	Inline
Contact Retention Within Housing	Without
Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	6.35 mm [.25 in]
Housing Material	PA 6.6

Usage Conditions

Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL, VDE
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	1200
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant











China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer






This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 <p>TE Part # 1-480703-3 04P UMNL CAP HSG ORNG</p>	 <p>TE Part # 1-480702-1 04P UMNL PLUG HSG BRN</p>	 <p>TE Part # 1-480703-4 04P UMNL CAP HSG YELL</p>	 <p>TE Part # 350779-4 04P UMNL PLUG HSG UL94VO</p>
 <p>TE Part # 350720-4 09P UMNL PLUG HSG UL94VO</p>	 <p>TE Part # 350780-1 04P UMNL CAP HSG</p>	 <p>TE Part # 926298-5 UN-MNL STECK-GEH 4P</p>	 <p>TE Part # 926305-6 UNML4WAY CAP</p>



Also in the Series | **Universal MATE-N-LOK**





Wire-to-Board Headers & Receptacles
(285)


Customers Also Bought




TE Part #5042433001
FLT0111-1.50-0



TE Part #1-104257-4
15 MTE RCPT HSG SR LATCH .100




TE Part #280232-6
250 FASTON POST INS.,REC.,1 POS,
NATRUAL




TE Part #626065
2 P FASTIN-ON 110 HOUSING TAB
PA66 NAT



TE Part #2-1419142-2
PE014003



TE Part #1623750-6
ER58 15K 5% AMMO




TE Part #3-1879665-8
H8 30K1 0.1% 15PPM



TE Part #2-2205132-4
CA MINI IO MINI IO TYPE II



TE Part #2-2205132-6
CA MINI IO MINI IO TYPE II



TE Part #2362520-1
IDC HANDTOOL PLUS AMP DP 2.5
MARK II

Documents

Product Drawings

[04P UNIV.M-N-L.PLUG](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_926298-3_F.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_926298-3_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_926298-3_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

German

Agency Approvals

[UL](#)

English