



Feed through terminal blocks

Screw clamp to quick-connect, DIN 1-3

Quick
connect




M 4/6.2G




BAM2




FEM6G




SCF6G




CBM...




BJMI6




M 4/6.3G



BAM2



FEMG



BJMI6

M 4/6.2G - 4 mm² blocks - 6 mm .236" spacing

Characteristics

Wire size (Screw clamp) mm ² / AWG	Solid Stranded	IEC NFC DIN	UL	CSA
		0.5 - 4 mm ² 0.5 - 4 mm ²	22-10 AWG	24-12 AWG
Wire size (quick-connect) mm ² / AWG	Quick-connect	2.8 x 0.8 mm series 110 - 1.5 mm ² max. 6.3 x 0.8 mm series 250 - 2.5 mm ² max.		
Voltage	V	750 V Gr.C	600	300
Current	A	25	20	25
Rated wire size	mm ² / AWG	4 mm ²	10 AWG	12 AWG
Wire stripping length	mm / inches	9.5 mm / .374"		
Recommended torque	Nm / lb.in	0.4-0.6 Nm / 3.5-5.3 lb.in		

Selection

Description	Type	Order P/N	Packaging
Terminal block with partition. Output : Screw clamp to horizontal quick connect tabs	grey ☐ blue ☐ beige V0 ☐	M 4/6.2G M 4/6.2G.N M 4/6.2G.V0	0115 189.11 0125 189.13 0195 189.12

Accessories

End stop	BAM2	9.9 mm	0206 351.16	50
End section	grey ☐ blue ☐ beige V0 ☐	FEM6G FEM6G FEM6G	2.5 mm 2.5 mm 2.5 mm	0113 027.07 0123 027.01 0193 027.00
Separator end section	grey ☐	SCF6G	3 mm	0113 075.17
Assembled jumper bar (with IP20 protection)	2 poles 3 poles 4 poles 5 poles 10 poles	BJMI6 BJMI6 BJMI6 BJMI6 BJMI6	32 A 32 A 32 A 32 A 32 A	0176 663.00 0176 664.01 0176 665.02 0176 666.03 0176 667.04
Shield connector	CBM5 CBM8	0.5 mm 0.8 mm	0178 745.14 0178 746.15	50 50

M 4/6.3G - 4 mm² blocks - 6 mm .236" spacing

Characteristics

Wire size (Screw clamp) mm ² / AWG	Solid Stranded	NFC DIN	UL	CSA
		0.2 - 4 mm ² 0.22 - 4 mm ²	—	20-12 AWG
Wire size (quick-connect) mm ² / AWG	Quick-connect	2.8 x 0.8 mm series 110 - 1.5 mm ² max. 6.3 x 0.8 mm series 250 - 2.5 mm ² max.		
Voltage	V	500 V Gr.C	—	300
Current	A	25	—	25
Rated wire size	mm ² / AWG	4 mm ²	—	12 AWG
Wire stripping length	mm / inches	9.5 mm / .374"		
Recommended torque	Nm / lb.in	0.5-0.8 Nm / 4.4-7.1 lb.in		

Selection

Description	Type	Order P/N	Packaging
Terminal block with partition. Output : Screw clamp - vertical quick-connect tabs to vertical quick-connect tabs	grey ☐	M 4/6.3G	0115 279.02


Accessories

End stop	grey	BAM2	9.9 mm	0206 351.16	50
End section	grey ☐	FEMG	1.5 mm	0114 144.12	25
Assembled jumper bar (with IP20 protection)	2 poles 3 poles 4 poles 5 poles 10 poles	BJMI6 BJMI6 BJMI6 BJMI6 BJMI6	32 A 32 A 32 A 32 A 32 A	0176 663.00 0176 664.01 0176 665.02 0176 666.03 0176 667.04	10 10 10 10 10


6

Quick-connect terminal blocks

Quick-connect to quick-connect, DIN 1-3




M 2,5/6.2G.2G




BAM2



FEM6G




SCF6G




CBM...




BJMI6




M 2,5/6.4G.1



BAM2



FEMG



BJMI6

M 2,5/6.2G.2G - 2,5 mm² blocks - 6 mm .236" spacing

Characteristics

		IEC NFC	DIN	UL	CSA
Wire size mm ² / AWG	Quick-connect	2.8 x 0.8 mm series 110 - 1.5 mm ² max. 6.3 x 0.8 mm series 250 - 2.5 mm ² max.			
Voltage	V	630	600	300	
Current	A	20	25	20	
Rated wire size	mm ² / AWG	2.5 mm ²	10 AWG	12 AWG	

Selection

Description	Type	Order P/N	Packaging
Standard block, outputs : horizontal quick-connect tabs to horizontal			
quick-connect tabs grey ☐	M 2,5/6.2G.2G	0115 191.03	50
beige V0 ☐	M 2,5/6.2G.2G.V0	0195 191.04	50

Accessories

End stop	grey	BAM2	9.9 mm	0206 351.16	50
End section	grey ☐	FEM6G	2.5 mm	0113 027.07	20
	beige V0 ☐	FEM6G	2.5 mm	0193 027.00	20
Separator end section	grey ☐	SCF6G	3 mm	0113 075.17	20
	grey V0 ☐	SCF6G	3 mm	0193 075.10	20
Assembled jumper bar (with IP20 protection)	2 poles	BJMI6	32 A	0176 663.00	10
	3 poles	BJMI6	32 A	0176 664.01	10
	4 poles	BJMI6	32 A	0176 665.02	10
	5 poles	BJMI6	32 A	0176 666.03	10
	10 poles	BJMI6	32 A	0176 667.04	10
Shield connector	CBM5	0.5 mm	0178 745.14	50	
	CBM8	0.8 mm	0178 746.15	50	

M 2,5/6.4G.1 - 2,5 mm² blocks - 6 mm .236" spacing

Characteristics

		IEC NFC	DIN	UL	CSA
Wire size mm ² / AWG	Quick-connect	2.8 x 0.8 mm series 110 - 1.5 mm ² max. 6.3 x 0.8 mm series 250 - 2.5 mm ² max.			
Voltage	V	630	600	300	
Current	A	35	25	25	
Rated wire size	mm ² / AWG	2.5 mm ²	10 AWG	12 AWG	

Selection

Description	Type	Order P/N	Packaging
Terminal block with partition. Output : vertical quick-connect tabs to vertical quick-connect tabs grey ☐	M 2,5/6.4G.1	0115 280.20	50

Accessories

End stop	grey	BAM2	9.9 mm	0206 635.16	50
End section	grey ☐	FEMG	1.5 mm	0114 144.12	25
Assembled jumper bar (with IP20 protection)	2 poles	BJMI6	32 A	0176 663.00	10
	3 poles	BJMI6	32 A	0176 664.01	10
	4 poles	BJMI6	32 A	0176 665.02	10
	5 poles	BJMI6	32 A	0176 666.03	10
	10 poles	BJMI6	32 A	0176 667.04	10