

5552212-1 ✓ ACTIVE

CHAMP


TE Internal #: 5552212-1

14 Position D-Shaped Connector, Receptacle, Cable-to-Board,  
Board Mount, 2.16 mm [.085 in] Centerline, Printed Circuit Board,  
Signal

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Receptacle Assembly: Vertical, 2.16mm



Number of Positions: 14

Connector & Housing Type: Receptacle

Connector System: Cable-to-Board

Connector Mounting Type: Board Mount

Centerline (Pitch): 2.16 mm [.085 in]

[All D-Sub Receptacle Assembly: Vertical, 2.16mm \(5\)](#)

## Features

### Product Type Features

Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Number of Positions	14
Number of Rows	2
PCB Mount Orientation	Vertical

### Body Features

Primary Product Color	Black
Connector Profile	Standard

### Contact Features

	30 μin
Contact Underplating Material	Palladium Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
Contact Options	Installed



### Termination Features

	.18 in
Rectangular Termination Post & Tail Width	.5 mm[.019 in]
Rectangular Termination Post & Tail Thickness	.25 mm[.01 in]
Termination Method to PCB	Through Hole - Solder

### Mechanical Attachment

Mounting Feature Material	Thermoplastic
Connector Mounting Type	Board Mount
PCB Mount Retention	Without
Mating Retention	With
Mating Retention Type	Bail Lock, Screwlocks

### Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2.16 mm[.085 in]

### Dimensions

PCB Thickness (Recommended)	1.57 mm, 2.36 mm, 3.18 mm[.062 in][.093 in][.125 in]
Row-to-Row Spacing	4.3 mm[.169 in]

### Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Shielded	No
Circuit Application	Signal

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	105
Packaging Method	Tray

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Customers Also Bought



TE Part #822796-SF  
RT8132-50-0M5




TE Part #NB17264001  
RP-4800-NO.10-0-SP



TE Part #5-104361-1  
02 MTE HDR SRRR LATCH W/HLDWN



TE Part #292172-6  
CT POST HDR ASSY 6P IN-TUBE BL




TE Part #350759-5  
02P UMNL HDR ASSY PC V2 LF



TE Part #1-640453-0  
10P MTA100 HDR ASSY SQ R/A



TE Part #1474640-8  
FSP-24Z-6



TE Part #1586317-4  
VAL-U-LOK SKT PHBZ AU 26-22 LP



## Documents

### Product Drawings

[ASSY, RCPT, 14 POS, VERT MTG](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_5552212-1\\_A.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_5552212-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5552212-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.