

NSYPLAZT15126G

Floor standing polyester enclosure, Thalassa PLA, open bottom, ventilated canopy, 1500x1250x620mm, IP44, IK10

Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or component type	Suitable enclosure
Version	PLAZT
Nominal height	1500 mm
Nominal width	1250 mm
Nominal depth	620 mm
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy 1 plinth

Complementary

Body type	Open top and bottom part assembled with side parts
Door type	Plain front
Number of doors	2 door(s)
Door opening side	Right and left (180 °)
Lock type	4 points lock, handle with 5 mm double bar insert
Accessibility for operation	Rear Top Front Bottom
Removable parts	Door by hinges Rear panel by fixing element Canopy by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	Veritas
Electrical insulation class	Class II

Environment

IP degree of protection	IP44 conforming to IEC 60529 (with plinth type open bottom part and ventilated canopy)
IK degree of protection	IK10 conforming to IEC 62262 (plain door)
Fire resistance	960 °C conforming to IEC 62208
Ambient air temperature for storage	-35...90 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
SCIP Number	1341ad4e-77b9-40e3-bab0-32043fbc5959
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No