

2312212-1 ✓ ACTIVE

NanoMQS | Nano MQS

TE Internal #: 2312212-1

12 V, 12 Position, Automotive Receptacle, Cable-to-Board / Cable-to-Cable, 1.8 mm [.071 in] Centerline, Black, Wire & Cable, Signal, Nano MQS

[View on TE.com >](#)



Automotive Parts > Automotive Connectors > Automotive Housings



Nominal Voltage Architecture: 12 V

Connector & Housing Type: Receptacle

Number of Positions: 12

Sealable: No

Operating Temperature Range: -40 – 105 °C [-40 – 221 °F]

Features

Product Type Features

Connector Shape	Rectangular
Mixed & Hybrid Connector	No
Connector & Housing Type	Receptacle
Sealable	No
Primary Locking Feature	Locking Lance
Connector System	Cable-to-Board, Cable-to-Cable
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	12
Number of Rows	2

Electrical Characteristics

Nominal Voltage Architecture	12 V
------------------------------	------

Body Features

Primary Product Color	Black
-----------------------	-------



Connector & Keying Code	A
-------------------------	---

Contact Features

Contact Size	.5mm
Contact Type	Receptacle
Mating Tab Width	.5 mm [.02 in]
Contact Current Rating (Max)	7 A

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF10
Centerline (Pitch)	1.8 mm [.071 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
Operating Temperature (Max)	105 °C [221 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 2317507-1
2X6POS,NANOMQS,HDR ASSY,
90DEG,SMD,COD A



TE Part # 2317527-1
2X6POS,NANOMQS,HDR ASSY,
180DEG,SMD,COD A



TE Part # 1-2395006-1
12POS,TAB0.5X0.4,HDR ASSY,
180DEG,COD A



TE Part # CAT-M8793-T273
MQS, RECEPTACLE AND TAB

Also in the Series | Nano MQS



Automotive Connector Caps & Covers
(2)



Automotive Connector Locks &
Position Assurance(3)



Automotive Housings(118)




Automotive Seals & Cavity Plugs(1)



Automotive Signal & Power Connector
Housings(118)



Automotive Signal & Power Headers
(60)



Automotive Terminals(11)

Customers Also Bought



Documents

Product Drawings

12POS,NANOMQS,REC HSG,COD A

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2312212-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2312212-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2312212-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



[Application Specification](#)

English

[Application Specification](#)

English