






PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 10:07 (UTC)



70BER10H

ROBUST Series Ultra High-Speed Angular Contact Ball Bearings



Parts Number

70BER10HTV1VSUELP3

Boundary Dimensions

	BER: 25°		Bearing Type
d	70	mm	Bore diameter
D	110	mm	Outside diameter
B	20	mm	Width
BN	4.0	mm	
SN	12	mm	
SB	1.4	mm	
r(min.)	1.1	mm	Chamfer Dimension
r1(min.)	0.6	mm	Chamfer Dimension

Basic Load Ratings

Cr	26.9	kN	Basic Dynamic Load Rating
C0r	18.1	kN	Basic Static Load Rating

Speeds

Grease	17800	min-1	Limiting Speed
Oil (Oil-air)	27800	min-1	Limiting Speed

Dimensions

	25°		Contact Angle
a	30.8	mm	Effective Load Center

Abutment and Fillet Dimensions

da(min.)	77	mm	Diameter of Shaft Abutment
Da(max.)	103	mm	Diameter of Housing Abutment
Db(max.)	105	mm	Diameter of Housing Abutment
ra(max.)	1	mm	Radius of Shaft or Housing Fillet
rb(max.)	0.6	mm	Radius of Shaft or Housing Fillet

Performance

Pa	22.6	kN	Permissible Axial Load
----	------	----	------------------------



PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 10:07 (UTC)



Table A		EL	L	M	H
	15°	6.5	6.0	5.0	4.5
	25°	2			
	30°	1.4			

Table B	DBD	DBB
Preload factor	1.36	2
Axial rigidity	1.48	2
Radial rigidity	1.54	2

Calculation of radial rigidity
Multiply axial rigidity by the appropriate factor in Table A.

Calculation of preload and axial rigidity for combined bearings
Multiply by the appropriate factor in Table B. For radial rigidity, multiply the value from Table A with the appropriate factor in Table B.

Preload,Rigidity(DB and DF arrangement)

	Preload	Axial Rigidity	Measured axial clearance
EL	49N	100N/μm	0μm
L	451N	212N/μm	-10μm
M	942N	278N/μm	-18μm

Additional information

2.6	g/brg	Recommended Grease Quantities
-----	-------	-------------------------------

Mass

0.605	kg	Mass(approx.)
-------	----	---------------