

TM-RIBBON 40 BK 105 - Ink ribbon

1259008

<https://www.phoenixcontact.com/gb/products/1259008>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, for the E-WMS... product group in combination with the THERMOMARK E.SLEEVE applicator and the WMS... and WMS-2 HF... product groups in combination with conventional roll printers, length: 300 m, roll length: 300 m, width: 40 mm, color: black

Product description

The TM-RIBBON 40 BK 105 is a thermal transfer ink ribbon, which is suitable for automated processing with the THERMOMARK E.SLEEVE applicator in combination with the THERMOMARK E.300 (D) / 600 (D) printers and the markers from the E-WMS... product family. Alternatively, the ink ribbon can also be used without the applicator for the identification of the E-WMS material or the WMS... and WMS-2 HF... product groups

Your advantages

- The TM-RIBBON 40 BK 105 thermal transfer ink ribbon is suitable for automated processing with the THERMOMARK E.SLEEVE applicator
- For efficient use of the entire ink ribbon, the width is optimally tailored to the E-WMS..., WMS..., and WMS-2 HF... product groups
- When combined with the right shrink sleeve, the printing is highly resistant to solvents and mechanical influences

Commercial data

Item number	1259008
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG1223
Product key	BG1223
GTIN	4063151367978
Weight per piece (including packing)	136.6 g
Weight per piece (excluding packing)	136.6 g
Customs tariff number	96121020
Country of origin	JP

TM-RIBBON 40 BK 105 - Ink ribbon



1259008

<https://www.phoenixcontact.com/gb/products/1259008>

Technical data

Product properties

Product type	Ink ribbon
Scope of delivery	Ink ribbon

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Dimensions

Width	40 mm
Length	300 m
Length of roll	300 m

Material specifications

Color	black (RAL 9005)
Material	Polyolefin-compatible ink coating

Environmental and real-life conditions

Ambient conditions

Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	24 months after production date.

TM-RIBBON 40 BK 105 - Ink ribbon

1259008

<https://www.phoenixcontact.com/gb/products/1259008>



Classifications

ECLASS

ECLASS-13.0	19140614
-------------	----------

ETIM

ETIM 9.0	EC001694
----------	----------

TM-RIBBON 40 BK 105 - Ink ribbon

1259008

<https://www.phoenixcontact.com/gb/products/1259008>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk