

Data sheet

Commercial Art.No.: R1.190.1340.0

Configurable control component SP-COP2-ENI-P-C DC 24V

samosPRO-Compact module, 16 safe inputs, 4 safe outputs, 4 configurable safe I/O, presses, USB-Interface, Industrial-Ethernet Profinet IO + Ethernet/IP + ModbusTCP, Pluggable push-in-terminals



Commercial Art.No.	R1.190.1340.0
EAN	4049088366628
Order Unit	1

Certificates / Approvals



Technical data

General

Suited for safety functions	Yes
Number of HW-interfaces industrial Ethernet	1
Number of HW-interfaces USB	1
Supporting protocol for EtherNet/IP	Yes
Supporting MODBUS protocol	Yes
Supporting protocol for PROFINET IO	Yes
Supporting TCP/IP protocol	Yes
SIL according to IEC 61508	3
Type of data transmission	Serial
Networkability	No
Erweiterbar	Yes
Programmable	Yes
In-/outputs configurable	Yes

Connection Data

Type of electric connection	Spring clamp connection
Detachable clamps	Yes

Application

With automatic closing	Yes
Function contactless working protection installation	Yes
Function operating mode selection	Yes

Function emergency stop	Yes
Function contactor monitoring	Yes
Function restart blockage	Yes
Function acces control	Yes
Function affirm pushbutton	Yes
Function 2-hand switching	Yes
On delay timer	Yes
Off delay timer	Yes

Output circuit

Number of outputs	8
Output current	4 A
Short-circuit protection, outputs	Yes
Type of digital output	Transistor
Min. allowed output voltage	16.2 V
Max. allowed output voltage	30 V
Number of digital outputs, integrated	8

Control circuit

Min. rated DC voltage for controls	15.6 V
Max. rated DC voltage for controls	30 V
Number of inputs	16
Input current with signal 1	2.3 mA
Permitted voltage at input	30 V

Supply circuit

Min. supply voltage	16.8 V
Max. supply voltage	30 V

Dimensions

Depth	115 mm
Width	45 mm
Height	96 mm

Classification

ECLASS 8.1	27243101
ETIM 7.0	EC002538
ETIM 6.0	EC002538
ETIM 5.0	EC002538
ETIM 4.0	EC002538

Safety parameters

Category (ISO 13849-1)	4
PL (ISO 13849-1)	Level e
SIL _{CL} (IEC 62061)	3
HFT	1
T _M	20 a
Note	More safety characteristics can be found in the manual.