



PTC without thermostat Wall mounting fan heater CS130 120 V AC, 1200 W

Model		
product brand name	SIVACON	
product designation	heater unit	
design of the product	Semiconductor, without thermostat	
General technical data		
consumed active power rated value	1 200 W	
volume flow rate free-blowing	160 m³/h	
Voltage		
type of voltage of the operating voltage	AC	
continuous heating power at 20 °C	1 200 W	
inrush current typical	16 A	
operating voltage		
• at AC at 50 Hz rated value minimum	120 V	
• at AC at 50 Hz rated value maximum	120 V	
• at AC at 60 Hz rated value minimum	120 V	
• at AC at 60 Hz rated value maximum	120 V	
Protection class		
protection class IP	IP20	
Main circuit		
operational current of the slow-blow fuse link	10 A	
Product details		
product component		
• blower	Yes	
• thermostat	No	
Connections		
tightening torque with screw-type terminals maximum	0.8 N·m	
type of connection technology	2-pole max. 2.5 mm² with strain relief	
Mechanical Design		
height	182 mm	
width	160 mm	
depth	120 mm	
fastening method	Clip fixing for 35 mm for DIN rail or screw fixing (M6)	
mounting position	air flow direction vertical (air exits on top/connection at bottom)	
net weight	1.2 kg	
material of the enclosure	plastic	
Environmental conditions		
relative humidity reference value	90 %	
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Con-  
firmations](#)

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2151-3B>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2151-3B>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MR2151-3B](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2151-3B)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>



last modified:

5/24/2025



