



MINI-MATCH

TE Internal #: 5164711-4
PCB Mount Receptacle, Right Angle, Board-to-Board, 4 Position,
2.5 mm [.098 in] Centerline, Tin (Sn), Through Hole - Solder, Signal,
Box

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**
PCB Mount Orientation: **Right Angle**
Connector System: **Board-to-Board**
Number of Positions: **4**
Centerline (Pitch): **2.5 mm [.098 in]**

Features

Product Type Features

PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Stackable	No
PCB Mount Orientation	Right Angle
Number of Positions	4

Electrical Characteristics

Operating Voltage	354 VAC
Insulation Resistance	1 MΩ

Contact Features

Contact Mating Area Plating Material Thickness	1.27 μm[50 μin]
PCB Contact Termination Area Plating Material Thickness	3.04 – 5.08 μm[120 – 200 μin]
Contact Layout	Inline
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin



Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Socket
Contact Current Rating (Max)	7 A

Termination Features

Rectangular Termination Post & Tail Width	.79 mm[.031 in]
Rectangular Termination Post & Tail Thickness	.5 mm[.02 in]
Termination Post & Tail Length	3.2 mm[.126 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Alignment Type	Polarizing Tab
PCB Mount Retention Type	Solder Tail
PCB Mount Alignment Type	Post Polarization
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Mating Entry Location	Side
Housing Material	Thermoplastic
Centerline (Pitch)	2.5 mm[.098 in]

Dimensions

	1.27 in
--	---------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	5000
Packaging Method	Box



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





TE Part #154763-E
SMCB 12 M AB VV 7-03 CL * 0007 137 E004




TE Part #474192-E
MSPEED 91 F SMD F6 B A-G VVV 137 094 *



TE Part #5161500-4
minimatch 4 pos male



TE Part #224513-E
MSPEED 50 F SMDTHR F6 * AB VV 137 094 *




TE Part #224558-E
MSPEED 50 M SMDTHR M2 * AB VV 137 094 *



TE Part #640466-1
05P UMNL PIN HDR ASSY V2 NATL



TE Part #5164711-3
03pos.MINI-MATCH FBTB, 2.5mm pitch



TE Part #474191-E
MSPEED 91 M SMD M2 B A-G VVV 137 176 *



TE Part #1-338068-0
MICRO-MATCH FTE,10P



TE Part #1-5164713-4
14P.MINI-MATCH ASSY

Documents

Product Drawings

04pos.MINI-MATCH FBTB, 2.5mm pitch

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5164711-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5164711-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5164711-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Product Specification

Mini Match Connection System

English

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

German