



 PRODUCT-DETAILS

OT1200U22

OT1200U22 SWITCH-DISCONNECTOR



General Information

Extended Product Type	OT1200U22
Product ID	1SCA105663R1001
EAN	6417019400051
Catalog Description	OT1200U22 SWITCH-DISCONNECTOR
Long Description	4-pole, front operated, base mounted non-fusible disconnect switch, handle and shaft are not included, terminal bolt kit included

ABB EcoSolutions

End Of Life Disassembling Instructions	1SCC301120M0201
Environmental Information	1SCC301233D0201
Environmental Product Declaration - EPD	1SCC301300D0201

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301047M0213
Mechanical Drawings	1SCC307757F0001 1SCC307756F0001 OT800-1200U22.stp OT1600E22.igs
Environmental Product Declaration - EPD	1SCC301300D0201

Environmental

Degree of Protection	Front IP00
Environmental Information	1SCC301233D0201
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country or Territory of Origin	Finland

Dimensions

Product Net Width	414.5 mm
Product Net Height	372 mm
Product Net Depth / Length	145.5 mm
Product Net Weight	22.2 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	400 mm
Package Level 1 Depth / Length	435 mm
Package Level 1 Height	170 mm
Package Level 1 Gross Weight	23.2 kg

Package Level 1 EAN

6417019400051

Technical

Degree of Protection	Front IP00
Distance Between Phases	Standard
Fourth Pole Position	Right Side
Fourth Pole Type	Switched - Simultaneous Function
Handle Type	Handle and shaft not included
Mechanical Durability	6000
Mounting Type	Base mounting
Number of Poles	4P
Operating Mode	Front
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Power Loss	at Rated Operating Conditions per Pole 48 W
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 1600 A (500 V) 1600 A (690 V) 1600 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 1250 A (500 V) 1250 A (690 V) 1250 A
Rated Operational Power AC-23A (P_e)	(380 ... 415 V) 710 kW (500 V) 900 kW (690 V) 1200 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 92 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 50 kA
Special Functions	No
Standards	IEC 60947-3 / UL 98 / CSA C22.2 NO.4
Switches Operating Mechanism	Mechanism Between the Poles 22 (Between the Poles)
Terminal Type	Lug terminals
Tightening Torque	acc. IEC 60947-1 56.5 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA	600 V
Ampere Rating	1200 A
Tightening Torque	acc. IEC 60947-1 56.5 N·m
Tightening Torque UL/CSA	500 in·lb

Certificates and Declarations

ATEX Certificate	No certification needed
Declaration of Conformity - CE	1SCC301155D2704
UL Certificate	cULus certificate OT800-1200
VDE Certificate	No certification needed

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122233
IDEA Granular Category Code (IGCC)	5290 >> Disconnect switch
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

