

End plate CPX-AP-A-EPLI-S

Part number: 8129249

FESTO



 General operating condition

Data sheet

Feature	Value
Dimensions (W x L x H)	48.4 mm x 117.2 mm x 61.5 mm
Type of mounting	On DIN rail via accessories On mounting frame Via through-hole for M5 screw Via through-hole for M6 screw
Product weight	256 g
Mounting position	Any, on H-rail: horizontal
Ambient temperature	-20 °C ... 50 °C
Note on ambient temperature	Observe ambient temperature derating according to IEC 61131-2:2017
Storage temperature	-20 °C ... 70 °C
Relative air humidity	5 - 95% Non-condensing
Nominal altitude of use	≤ 2000 m ASL (> 79.5 kPa)
Max. installation height	3500 m
Note on max. installation height	Observe ambient temperature derating according to IEC 61131-2:2017
Corrosion resistance class CRC	1 - Low corrosion stress
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Note on vibration resistance	SG1 on DIN rail SG2 on direct mounting Transport application test with severity class 1 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Note on shock resistance	30 g/11 ms to EN 60068-2-27 SG1 on DIN rail SG2 on direct mounting Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Protection class	III
Pollution degree	2
Overvoltage category	II
Max. cable length	50 m system communication
LABS (PWIS) conformity	VDMA24364-B2-L
Fire test material	UL94 V-0 (housing)
Note on materials	RoHS compliant Free of halogen Free of phosphoric acid ester
Material housing	Coated die-cast aluminium
Material cover	Reinforced PBT
Material screws	Nickel-plated steel Galvanised steel

Feature	Value
Material seals	Polyurethane foam
Material o-ring	Fluoro rubber
Diagnostics via LED	Diagnostics per module Power supply, electronics/sensors Load power supply
Diagnostics per internal communication	Communication error Electronics/sensors overvoltage Load overvoltage Electronics/sensors undervoltage Load undervoltage
Communication interface, function	System communication XF10 IN / XF20 OUT
Communication interface, connection type	2x socket
Communication interface, connection technology	M8x1, D-coded according to EN 61076-2-114
Communication interface, number of pins/cores	4
Communication interface, plug pattern	00995937
Communication interface, protocol	AP
Communication interface, screened	Yes
Power supply, function	Incoming electronics/sensors and load
Power supply, connection type	Plug
power supply, connection system	M8x1, A-coded to EN 61076-2-104
Power supply, connection pattern	00991171
Power supply, number of pins/wires	4
Power transmission, function	Outgoing electronics/sensors and load
Power transmission, connection type	Socket
Power transmission, connection technology	M8x1, A-coded to EN 61076-2-104
Power transmission, number of pins/wires	4
Power transmission, plug pattern	00991872
Note regarding operating voltage	SELV/PELV fixed power supplies required Note the voltage drop
Note on nominal operating voltage DC	2x24 V [XD1,PS,PL] Protected Extra-Low-Voltage to IEC 60204-1
Nominal operating voltage DC of load	24 V
Permissible voltage fluctuation of load	±25%
Nominal DC operating voltage, electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	±25%
Power supply, conductor diameter	0.5 mm ²
Nominal current	4 A
Max. power supply	2 x 4 A (external fuse required)
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 41 mA
Intrinsic current consumption at nominal operating voltage load	Typically 3 mA
Power failure bridging	10 ms
Potential separation between the supply voltages electronics/sensor technology and load/valves	Yes
Reverse polarity protection	Yes