




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: .32 – .82 mm²

Mating Tab Width: 4.75 mm [.187 in]

Mating Tab Thickness: .51 mm [.02 in]

Features

Product Type Features

Terminal Features	Wire Stop
Insertion Force	Normal

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Insulation Material	Nylon
---------------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight



Contact Base Material	Phosphor Bronze
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Closed

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	21.75 mm[.855 in]
Compatible Insulation Diameter Range	3.43 mm[.135 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.32 – .82 mm²

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	2700
Packaging Method	Strip/Reel

Other

Barrel Color	Red
--------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JUNE
2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 7-2151034-7
OCEAN_2.0_SPARE_PART_KIT-176O

TE Part # 58628-2
PROCIMP DIESET 26-14 ULTRAFast

TE Part # 90390-3
DIES ULTRA-FAST FASTON 22-18 DIE SET

TE Part # 2151034-2
OCEAN_2.0_APPLICATOR-S-176O-SSA

TE Part # 58628-1
PROCIMP T&D 26-14 ULTRAFast

TE Part # 58078-3
TETRA CRIMP FRAME W/O DIES

Also in the Series | [Ultra-Fast 187](#)



Quick Disconnects(47)

Customers Also Bought



ANVIL REPRESENTATION ONLY

TE Part #4-1803060-8
ANVIL, COMBINATION, NO JOG, END FEED



TE Part #61944-2
250 FASTON REC 18-14 AWG TPBR



CRIMPER REPRESENTATION ONLY

TE Part #8-2119582-3
CRIMPER, INSULATION F PREMIUM



TE Part #456409-8
CRIMPER WIRE .120 F



TE Part #1-6609020-1
20EB1=F7108 S0



TE Part #6-66460-2
PIN,.062 DIA,.025 SQ POST,LP



TE Part #350199-1
RING TONGUE TERMINAL 18-14 AWG NIPST



TE Part #CR2103-000
CPGI-WC-WG-OR-BULK



ANVIL REPRESENTATION ONLY

TE Part #4-1633932-5
ANVIL, COMBINATION



TE Part #52928-1
PIDG SP SPD 22-16COM22-18MIL 5

Documents

Product Drawings

ULTRA-FAST 187 ASY REC 22-18 TPPB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-520181-4_AD_c-2-520181-4-ad.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2-520181-4_AD_c-2-520181-4-ad.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-520181-4_AD_c-2-520181-4-ad.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ultra-Fast and Ultra Fast Plus](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English