

## **OLS-C02, G 1/2", Opened in media (SPST n.c.), 150 mm / ~ 5.9 inch mm**

### **OLS-C02, G 1/2", Opened in media (SPST n.c.), 150 mm / ~ 5.9 inch mm**

Item number:	31134006	
Quantity:	1 pcs.	
Order code:	OLS-C02-G10150Z-HNCM4-ZZZZZ-ZZZ	W101OLS2Z1LD
Overview:	OLS-C02, G 1/2", Opened in media (SPST n.c.), 150 mm / ~ 5.9 inch mm Optoelectronic level switch, with selectable switch length Model: OLS-C02 Process connection: G 1/2" insertion length: 150 mm / ~ 5.9 inch mm Output Signal: one switching output (PNP) Switch function: Opened in media (SPST n.c.) Power supply: 12 - 32 V DC Electrical connection: circular connector M12x1, 4-pin pin assignment el. connection: 1=U+, 3=U-, 4=SP Operating pressure: max. 25 bar Permissible medium temperature: -30...100 °C Wetted parts: Stainless steel 1.4571, borosilicate glass, silicone adhesive Specifications according to data sheet: LM 31.32	
Details:	OLS-C02, G 1/2", Opened in media (SPST n.c.), 150 mm / ~ 5.9 inch mm Optoelectronic level switch, with selectable switch length Model: OLS-C02 Process connection: G 1/2" insertion length: 150 mm / ~ 5.9 inch mm Output Signal: one switching output (PNP) Switch function: Opened in media (SPST n.c.) Power supply: 12 - 32 V DC Electrical connection: circular connector M12x1, 4-pin pin assignment el. connection: 1=U+, 3=U-, 4=SP Operating pressure: max. 25 bar Permissible medium temperature: -30...100 °C Wetted parts: Stainless steel 1.4571, borosilicate glass, silicone adhesive Specifications according to data sheet: LM 31.32	