

EUROCARD


TE Internal #: 1-148059-5

Receptacle, Board-to-Board, 96 Position, 2.54 mm [.1 in] Centerline,
Printed Circuit Board, 3 Row, Vertical, 32 Column, Eurocard
Connectors

[View on TE.com >](#)



Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Connector & Housing Type: **Receptacle**
Connector System: **Board-to-Board**
Termination Post & Tail Length: **17 mm [.669 in]**
Number of Positions: **96**
Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
DIN Size	Standard
DIN Level	II

Configuration Features

Number of Positions	96
Number of Rows	3
PCB Mount Orientation	Vertical
Number of Columns	32
Rows Loaded	A, B, C
Number of Signal Positions	96

Body Features

Primary Product Color	Gray
-----------------------	------



Contact Features

Contact Mating Area Plating Material	Tin-Lead
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Type	Socket
Contact Mating Area Plating Material Thickness	5.08 µm
Contact Current Rating (Max)	1.5 A

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	17 mm[.669 in]

Mechanical Attachment

Connector Mounting Type	Board Mount
Panel Mount Feature	Without
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention Type	Action/Compliant Tail
Mating Alignment	With
PCB Mount Alignment	Without
PCB Mount Retention	With

Housing Features

Housing Material	Polyester - GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	28.51 mm
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------



Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5536366-5
ASSY,PIN,EURO,TYPE C,LEAD-FREE,
% POS.,,

TE Part # 2-1393640-4
V42254B2102C960=PC612 FEDERLEI

TE Part # 650473-8
09% EURO TYPE C PIN ST ASSY

TE Part # 5536148-5
ASSY,PIN,ENH.TYPE C,EUROCARD,L-
FREE,5ROW



TE Part # 5536146-5
ASSY,PIN,ENH.TYPE C,EUROCARD,L-FREE,5 RO




TE Part # 650473-3
096 EURO TYPE C PIN ST ASSY




TE Part # 1-1393644-6
V42254B1100C960=PC612 MESSERLE



TE Part # 5148292-5
ASSY,RECEPTACLE,EUROCARD,TYPE




TE Part # 5535090-4
ASSEMBLY,RECEPTACLE,EUROCARD,T




TE Part # 5535032-4
ASSY,RECEPTACLE,EUROCARD,TYPE



TE Part # 3-1393641-1
V42254B2202C960=PC612 FEDERLEI




TE Part # 215605-4
96P.IEC-C MALE CONN




TE Part # 650461-4
096 EURO TYPE R RECPT ASSY




TE Part # 5650963-5
ASSY,RECEPTACLE,EUROCARD,TYPE



TE Part # 5650897-5
ASSY,RECEPT,EURO,TYPE R,L-FREE,A&C,64/96




TE Part # 5650963-4
ASSY,RECEPTACLE,EUROCARD,TYPE




TE Part # 5650470-5
ASSY,PIN,EUROCARD,TYPE R,LEAD-FREE,96 PO



TE Part # 5148116-5
ASSY,PIN,EUROCARD,TYPE C,LEAD-FREE,96 PO



TE Part # 5535090-5
ASSEMBLY,RECEPTACLE,EUROCARD,T




TE Part # 5536019-5
ASSY,PIN,EUROCARD,TYPE R,LEAD-FREE,96 PO

Customers Also Bought



TE Part #413170-E
STVH15 15 F ZD VV 3-00 F001 ** 197 E 01



TE Part #5745078-6
HD-20 RCPT 25P VERT FFSCRLK




TE Part #254960-E
STVE 160 F ABCDE VVVV 7-00 EEUE 17,0 *




TE Part #350737-1
12P UMNL PIN HDR ASSY 94VO 17,0 *







TE Part #204752-E
STVC 96 F ABC VV 7-00 EE 4,0 * 247 E007



TE Part #5745079-6
HD-20 RCPT 37P VERT FFSCRLK



TE Part #5206052-3
SCREW,SPECIAL,ZN



TE Part #5745077-6
HD-20 RCPT 15P VERT FFSCRLK



TE Part #484924-E
M12 MALE, A CODE, 5P, 10.5MM SMT

TE Part #244295-E
STVC 96 F ABC VV 7-00 EEUE 17,0 * 241 E

Documents

Product Drawings

096 EURO TYP C RECP 17MM ASSY

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-148059-5_K.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-148059-5_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-148059-5_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English