



2.4GHz WLAN YAGI Antenna + 16dB Antenna

- YAGI Antenna
- 2.4 - 2.5GHz
- Active gain: +16dB
- VSWR <2.0:1
- 'U' Bolts Fixing
- RG58 Connecting Lead
- N Type Connector
- Alternative Connectors:
FME / Mini-UHF / TNC
- Horizontal Polarization



Applications

- WLAN
- Range Extension

Description

A rugged high Gain Antenna for 2.4GHz / WLAN applications where high performance is required .

Part Numbers

| | Dimensions (mm) | Weight (Kg) | Mount | Connector |
|----------------------|-----------------|-------------|--------|-----------------|
| ANT-24PANEL14 | 770 x 295 x 570 | 0.55 | U bolt | 'N' Type Female |

R F Solutions Ltd. ,
Unit 21, Cliffe Industrial Estate,
Lewes, E. Sussex. BN8 6JL. England.

Email : sales@rfsolutions.co.uk <http://www.rfsolutions.co.uk>

Tel: +44 (0)1273 898 000 Fax: +44 (0)1273 480 661




2.4GHz WLAN YAGI Antenna + 16dB Antenna


- RG58 Connecting Lead
- 50ohm Impedance
- Horiz Bandwidth 35°
- Vertical Bandwidth 20°
- Operating Temp -30° to +60°
- Construction ABS
- Colour: Light Grey
- Max Wind Load 120Km/h'
- Max Power 200W

Antenna Gain Patterns


Horizontal



Vertical



Return Loss



SWR

