


DATA SHEET O-Ring 121150

PART INFORMATION

Part number	121150
Inside diameter d1	21,30 mm
Cross-section d2	3,60 mm
Size standard	R17
Tolerance range according to	ISO 3601-1
Rubber family	EPDM
Rubber compound	7EP1197
Quality acceptance criteria on aspect	ISO 3601-3



7EP1197 COMPOUND NFORMATION

Original characteristics

Hardness Sh A Tensile strength Elongation at break Compression set TR10 Brittle point Operational temperature range * Peak temperature 70 14 MPa 180 % 12 % (24h 150°C) -46 °C -55 °C -50 °C / 140 °C 175 °C

Rubber color

Black

Official agreements Food : FR, USA Potable water : DE, FR, GB, IT, NL, USA Hot a Drini SF6

* The temperature range is given as an indication and can be influenced by the environment, the fluids in contact and the operating conditions.



LE JOINT FRANCAIS SNC 1 rue Gutenberg ZI Ouest de Bazouges - 53200 CHATEAU-GONTIER - FRANCE www.oring.hutchinson.fr - oring@hutchinson.com

EPDM FAMILY

Very good resistance

Water, steam and water-based solutions Synthetic brake fluids Atmospheric agents Low temperature

Poor resistance

Mineral oils and hydrocarbons

Particularities

Fairly good mechanical behaviour

Typical applications

Hot and cold water taps Drinking water SF6 circuit breakers Cooling circuit Brake circuit Heating circuit

