




MY4ZN 24VDC (S)

Relay, plug-in, 14-pin, 4PDT, bifurcated contacts, 5 A, mech & LED indicators, label facility, 24 VDC

Specifications

Mounting method	With plug-in socket
Usage	General purpose
Poles	4
Rated carry current	5 A
Coil voltage	24 V
Operation voltage	DC
Contact material	Ag alloy + Au cladding
Contact description	4PDT
Features	Bifurcated contacts, LED, Transparent case, With mechanical indicator
Terminal type	Plug-in, Solder



PYF-14-PU

Socket, DIN rail/surface mounting, 31 mm, 14-pin, Push-in terminals



PYF-14-PU-L

Socket, DIN rail/surface mounting, 31 mm, 14-pin, Push-in terminals,



PYF14-ESN-B

Socket, with common and coil terminals on the bottom and with the NC & NO terminal on the top - Black.



PYF14-ESS-B

Socket, with coil terminals on the bottom and with the common and NC & NO terminals on the top - Black.



PYF14S

Socket, DIN rail mounting, 14-pin, screwless terminals



PYFZ-14-E

Socket, DIN rail/surface mounting, 14-pin, screw terminals (standard)

CAD Library



Industrial Relays Brochure

EN PDF 2.77 MB



MY(S) Miniature Power Relays Datasheet

EN PDF 9.24 MB



OMRON Manufacturing Know-How: High Quality Relays

Leaflet

EN PDF 449 KB



Solution case study No.8 Environment resistance

Brochure

EN PDF 623 KB