

USB-C Multiport Adapter with 4K HDMI - 2x USB-A Ports - 60W PD - Black

Product ID: DKT30CHPD



Turn your MacBook or Windows® laptop into a workstation, anywhere you go, with this USB-C™ multiport adapter with HDMI.

Connect a UHD 4K HDMI Monitor

Connect your USB-C or Thunderbolt 3 laptop to a 4K 30Hz monitor, using this USB-C video adapter to create a dual-display workstation. Get more work done with an additional display, allowing you to multitask more efficiently or connect your laptop to an HDMI projector or TV for presentations in a boardroom.

Charge Your Laptop

The portable laptop docking station features a USB-C Power Delivery port that lets you power and charge your USB-C laptop during a presentation or while you're working. It's perfect for port limited laptops with a single USB-C port. Even with the adapter connected to the laptop, you can still power and charge your laptop with a USB-C power adapter.

Enhance Productivity

The 4K HDMI adapter gives you the connections you need to get more work done. You can connect peripherals like a flash drive or mouse using the two USB 3.0 Type-A ports. You can also add wired network connectivity with the Gigabit Ethernet port, making it ideal in areas without Wi-Fi.

DKT30CHPD is TAA compliant and is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Note: To ensure full adapter functionality, your laptop's USB-C port must support USB Power Delivery and DP Alt Mode.

Certifications, Reports and Compatibility



Applications

- Connect to an external HDMI monitor for multitasking
- Deliver presentations on an HDMI TV or projector in a boardroom or classroom
- Connect to an HDMI TV in a hotel or hot desk space

Features

- Add an additional display with this UHD 4K capable USB-C HDMI multiport video adapter
- Power your laptop with 60W Power Delivery using a USB Type-C power adapter
- Add USB 3.0 Type-A devices, like a flash drive or mouse, through this multiport adapter
- Flexible desktop placement with the extended 34 cm attached USB-C cable
- Add wired network connectivity with the Gigabit Ethernet RJ45 port

Hardware	Warranty	3 Years
	4K Support	Yes
	Bus Type	USB-C
	Chipset ID	VIA/VLI - VL813 VIA/VLI - VL100 Chrontel - CH7525A ASIX - AX88179
	Displays Supported	1
	Fast-Charge Port(s)	No
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0 and 1.1
	Performance	Auto MDIX
	Compatible Networks	10/100/1000 Mbps
	Full Duplex Support	Yes
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
	Maximum Digital Resolutions	4096 x 2160p @ 24Hz or 3840 x 2160p (HDMI) @ 30Hz Lower resolutions are also supported.
	Type and Rate	USB 3.0 - 5 Gbit/s
	UASP Support	Yes
Connector(s)	Connector Type(s)	1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Male 1 - HDMI (19 pin) Female 1 - RJ-45 Female 2 - USB Type-A (9 pin) USB 3.0 Female 1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Female
Software	OS Compatibility	Windows® 7, 8, 8.1, 10 Mac OS® 10.9 to 10.14 Chrome OS™
Special Notes / Requirements	Note	Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure that your host USB-C port supports USB Power Delivery 2.0 and DP alt mode. The adapter can connect to a host laptop's USB-C port that doesn't support USB Power Delivery 2.0. However, in this configuration if a power adapter is connected to the multifunction adapter, it will not pass power through to your host laptop.

A 4K-capable display is required to achieve 3840 x 2160p resolution (4K is also known as 4K x 2K)

USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.

Your laptop might have specific charging requirements. For example, if your laptop requires exactly 60W of power and an adapter consumes some of the 60W, your laptop might not recognize that it is getting enough power. For more information about Power Delivery, refer to the manufacturer of your hardware.

System and Cable Requirements

A host laptop with an available USB-C port (to ensure full adapter functionality, the host USB-C port must support USB Power Delivery 2.0 and DP alt mode)

Optional: USB-C power adapter (for example, your laptop's USB-C based power adapter)

Power	Power Delivery	60W
	Power Source	USB-Powered
Environmental	Humidity	0~85% RH (Non-condensing)
	Operating Temperature	0°C to 50°C (32°F to 122°F)
	Storage Temperature	-10°C to 65°C (14°F to 149°F)
Physical Characteristics	Cable Length	13.7 in [348 mm]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.7 in [18 mm]
	Product Length	3.8 in [96 mm]
	Product Weight	2.3 oz [64 g]
	Product Width	2 in [51 mm]
Packaging Information	Shipping (Package) Weight	7 oz [198 g]
What's in the Box	Included in Package	1 - USB-C multiport adapter
		1 - quick-start guide

Product appearance and specifications are subject to change without notice.