


262A - Ribbed chisels, round head



Description:

- Forged chisels with rounded edges for better handling.

 • Cylinder-shaped head for safer
- impact.
- Cutting edge hardness: 57 to 59 HRc.
- Cutting edge angle: 60°.
- Presentation: zinc-plated finish.





=0	A [mm]	Length L [mm]	Weight [g]
262A.15	21.0	150.0	170.0
262A.18	24.0	180.0	250.0
262A.20	26.0	200.0	340.0
262A.25	29.0	260.0	500.0